




Witzlebenstr. 7 | 45472 Mülheim an der Ruhr, Germany
T +49 208 4952-0 | F +49 208 4952-264



Company / customer			
Project description			
Drawing number	ID 100004348;EG-VA805526/111-0600/3GD		
Commission			
Manufacturer (company)	Hans Turck GmbH & Co. KG	Manufacturer (company)	
Path		Path	
Project name	ID 100004348_V2	Protection class	
Make		Power supply	
Type		Supply line	
Place of installation		Control voltage	
Responsible for project	Hans Turck GmbH & Co. KG		
Part feature		Year of manufacture	
Created on	26.02.2019		
Edit date	25.01.2021	by (short name)	Claus.Vogel
		Number of pages	9

Parts list


SR. NO.	DEVICE TAG	QTY.	PART DESCRIPTION	MANUFACTURER	PART NUMBER	TYPE NUMBER
1	-CABINET_BASE	1	Cabinet (800 x 550 x 260)	ROSE Systemtechnik GmbH	ROSE.A17454-Unterteil	A17454-Unterteil
2	-CABINET_DOOR	1	Door with Window (800 x 550 x 260)	ROSE Systemtechnik GmbH	ROSE.A17454-Deckel	A17454-Deckel
3	-FLANGE_BREATHER	1	M20 Breather/Drainer with stainless steel castled nut	Redapt	RED.DP-E-4-0-04-S3	DP-E-4-0-04-S3
4	-FLANGE_GLAND_M16_BU	108	PU Gland Ex-e Blue M16	WISKA Hoppmann GmbH	WISKA.ESKE/1-i 16	ESKE/1-i 16
5	-FLANGE_GLAND_M20_BU	4	PU Gland Ex-e Blue M20	WISKA Hoppmann GmbH	WISKA.ESKE/1-i 20	ESKE/1-i 20
6	-FLANGE_GLAND_M25_BK	4	PU Gland Ex-e Black M25	WISKA Hoppmann GmbH	WISKA.ESKE/1-e 25	ESKE/1-e 25
7	-FLANGE_LEFT	1	Left Flange for ROSE cabinet 800x550x260	ROSE Systemtechnik GmbH	ROSE.FLANGE_80XX26_1X1_L_V2	FLANGE_80XX26_1X1_L_V2
8	-FLANGE_RIGHT	1	Right Flange for ROSE cabinet 800x550x260	ROSE Systemtechnik GmbH	ROSE.FLANGE_80XX26_1X1_R	FLANGE_80XX26_1X1_R
9	-MT	1	Remote I/O System excom® Module rack, zone 2, for 24 modules	Hans Turck GmbH	TUR.9100682	MT24-3G
10	-X1	2	End clamp	Phoenix Contact	PXC.3022276	CLIPFIX 35-5
11	-X1	2	Feed-through terminal block	Phoenix Contact	PXC.3044160	UT 10
12	-X1	2	Feed-through terminal block	Phoenix Contact	PXC.3044188	UT 10 BU
13	-X1	2	Ground modular terminal block	Phoenix Contact	PXC.3044173	UT 10-PE




DOOR VIEW



RIGHT VIEW



MOUNTING VIEW



LEFT VIEW

