

Customer-Specific RFID Label Tags

Status: April 2024

We need this information to be able to prepare a quotation that meets your requirements as accurately as possible. If we can provide you with assistance in filling out this form, please call us at any time (T +49 208 4952-380) or email us at: info@turck.com.

Customer/potential customer	Name			Customer no.	
Reason for the request	<input type="checkbox"/> A – new product	<input type="checkbox"/> B – existing product with changes	<input type="checkbox"/> C – existing product (unchanged)		
Improvement/modification to an existing product					
Total quantity with acceptance quantities for partial deliveries, if applicable					
Desired format		Width (mm)	x	Height (mm)	
Frequency	<input type="checkbox"/> 860–960 MHz (UHF)		<input type="checkbox"/> 13.56 MHz (HF)		
Standard	<input type="checkbox"/> Global <input type="checkbox"/> Etsi <input type="checkbox"/> FCC		<input type="checkbox"/> ISO 15693		
Antenna layout (if known)					For UHF: Designation/format (e.g. Tageos EOS-500) For HF: Designation/format (e.g. 45 × 76 mm, Circus)
Chip					(e.g. NXP UCODE 9, Impinj M730, NXP ICODE SLIX2)"
Materials					
▪ Laminate					(e.g. transparent PET)
▪ Outer material					(e.g. 80 g/m ² paper/PET, PP film)
▪ Color and design of carrier material (liner)					(e.g. standard)
▪ Adhesive	<input type="checkbox"/> Strong <input type="checkbox"/> Permanent <input type="checkbox"/> Removable	Description of the desired properties or name of the adhesive			
Adhesive substrate (please describe precisely if the adhesive is not known)					
If you do not know the material, please describe the application and requirements for the product. We need this information to prequalify the material.					
Print image: The layout must be provided in a suitable format when the order is placed.	<input type="checkbox"/> Without print <input type="checkbox"/> With print	<input type="checkbox"/> Layout provided <input type="checkbox"/> Sequential numbering, plain text <input type="checkbox"/> Sequential numbering, barcode	Number of colors		
	<input type="checkbox"/> Black mark	Black mark description: Size and placement. e.g.: 5 × 3 mm, between the labels, at the back of the carrier edge, on the right-hand side leaving the roll		Barcode type	
Special features (e.g. perforation lengthwise/widthwise or punching (control punchings))					
▪ Dimensions					
▪ Position (sketch, if necessary)					
Coding					
Packaging	<input type="checkbox"/> On roll			pieces per roll/max. External Ø	
	<input type="checkbox"/> Leporello-folded into			folds	
	<input type="checkbox"/> Loose	bundled into		pieces	
Defective part handling	<input type="checkbox"/> 100 % checked, defective parts marked (standard) <input type="checkbox"/> 100 % checked, defective parts marked (+ additional costs) <input type="checkbox"/> 100 % checked, defective parts marked (+ additional costs)				
Printer type					