


NI8-S18-AP6X-H1141
电感式传感器





技术数据

型号	NI8-S18-AP6X-H1141
货号	46526
常用数据	
额定开关距离	8 mm
安装条件	非齐平
安全工作距离	$\leq (0.81 \times S_n) \text{ mm}$
修正系数	37#钢 = 1; 铝 = 0.3; 不锈钢 = 0.7; 黄铜 = 0.4
重复精度	$\leq 2\%$ 满量程
温度漂移	$\leq \pm 10\%$
磁滞	3...15 %
电气数据	
工作电压 U_B	10...30 VDC
纹波电压 U_{ss}	$\leq 10\% U_{Bmax}$
额定直流工作电流 I_o	$\leq 200 \text{ mA}$
空载电流	$\leq 15 \text{ mA}$
漏电流	$\leq 0.1 \text{ mA}$
隔离测试电压	0.5 kV
短路保护	是/循环
I_o 时的压降	$\leq 1.8 \text{ V}$
断线/反极性保护	是/是
输出性能	3线, 常开触点, PNP
开关频率	0.5 kHz
机械数据	
设计	螺纹, M18 x 1
尺寸	53 mm
外壳材料	塑料, PA12-GF30

特点

- M18 x 1圆柱螺纹
- 塑料, PA12-GF30
- 3线直流, 10...30 VDC
- 常开, pnp输出
- M12 x 1接插件

接线图



功能原理

电感式传感器以非接触和无磨损的方式检测金属物体。以无磨损和非接触的方式检测金属物体。电感式传感器通过铁氧体线圈上构成的RLC线圈产生磁场。

技术数据

感应面材料	塑料, PA12-GF30
外壳螺母的最大拧紧扭矩	2 Nm
电气连接	接插件, M12 × 1
环境条件	
工作温度	-25...+70 °C
防震动性	55 Hz (1 mm)
防冲击性	30 g (11 ms)
防护等级	IP67
MTTF	2283 年 符合SN 29500 (Ed.99) 40 °C认证
开关状态指示	LED指示灯, 黄色



安装说明

安装说明/描述


The image contains three technical diagrams illustrating the installation of a sensor on a bracket. The top-left diagram shows a side view of a bracket with a circular hole and a threaded hole, with dimension T indicating the distance from the hole center to the edge. The top-right diagram shows two brackets with a sensor (yellow cylinder) mounted on one, with dimension G indicating the distance between the sensor and the bracket edge. The bottom diagram shows a bracket with two sensors mounted on it, with dimensions N, S, D, and W indicating various distances and widths.

距离D	$3 \times B$
距离W	$3 \times S_n$
距离T	$3 \times B$
距离S	$1.5 \times B$
距离G	$6 \times S_n$
距离N	$2 \times S_n$
B有效面积直径	$\varnothing 18 \text{ mm}$


附件

QM-18	6945102	BST-18B	6947214
		快速安装支架单端封闭；材料：铜镀铬外螺纹M24 × 1.5。注意: 使用快速安装支架时，接近开关的开关距离可能更改。	
			
		用于圆柱螺纹传感器的带塞子的安装夹具；材料：PA6	

MW18 6945004
用于圆柱螺纹传感器的安装托架；材料：不锈钢 A2 1.4301 (AISI 304)



BSS-18 6901320
用于平滑圆柱型和圆柱螺纹传感器的安装夹具；材料：PP



附件

尺寸图	型号	货号	
	RKC4T-2/TEL	6625010	连接线缆，M12母头接插件，直式3针，线缆长度2 m，护套材质PVC，黑色；cULus认证

