

Technical data

Housing material	Die-cast zinc
Electrical connection	Connector, M12 × 1
Axial shaft load	20 N
Radial shaft load	40 N
Environmental conditions	
Ambient temperature	-40...+85 °C
Vibration resistance (EN 60068-2-6)	300 m/s², 10...2000 Hz
Shock resistance (EN 60068-2-27)	300 m/s², 10...2000 Hz
Protection class	IP67
Protection class shaft	IP67

Accessories

Dimension drawing	Type	ID	
	RKC5701-5M	6931034	



Bus cable for CAN (DeviceNet, - CANopen), M12 female connector, straight, cable length: 5 m, jacket material: PUR, anthracite; cULus approval