


# Smart Power Supply Module in IP67

## 24...28 VDC Output Voltage

## 3-Phase, 25-A Output Current


## PSU67-3P-1S-2L-24250-F




Type	PSU67-3P-1S-2L-24250-F
ID	100028238
Nominal voltage	Universal voltage supply unit
Operating voltage	320...550 VAC
Frequency	50...60 Hz
Power dissipation, typical	≤ 23 W
PFC	0.95
Efficiency	95 %
External fuse	B-6A, C-6A
Internal fuse	V1 + V2 bridged
Nominal output voltage	24 V
Nominal current	25 A
Output power	600 W (up to +45 °C) 500 W (up to +55 °C) 350 W (up to +70 °C) 1000 W (+55 °C, up to max. 5 sec.) 700 W (+70 °C, up to max. 5 sec.)
Parallel mode	no
Ripple	100 mV
Short-circuit behaviour	Current limiting
Approval	CE cULus RoHS SEMI F47
Protection class	IP67
Ambient temperature	-25...+70 °C
Storage temperature	-40...+85 °C
Dimensions	183 x 180.6 x 58.7 mm
Weight	1200 g

- Broad temperature range
- Status LED
- High efficiency, > 95 %
- 3-phase AC input, M12 S-coded
- Current-limited outputs, 2 × M12 L-coded
- Protected by eFuse (V1 + V2 bridged)
- Relay contact for checking the DC status
- LED interface and control buttons for maximum flexibility

### Input assignment M12 S-coded (XD1)



### Output assignment M12 L-coded (XD2 and XD3)



### M12 Output-OK Assignment

