

Environmental conditions	
Ambient temperature	-40...+85 °C
Temperature changes (EN60068-2-14)	-40... +85 °C; 20 cycles
Vibration resistance (EN 60068-2-6)	20 g; 5 h/axis; 3 axes
Shock resistance (EN 60068-2-27)	150 g; 4 ms ½ sine
Protection class	IP68
	IP69K
MTTF	297 years acc. to SN 29500 (Ed. 99) 40 °C
Power-on indication	
	LED, Green
Measuring range display	LED, yellow
UL certificate	E351232

