


## FW-ERSSM0414-PS-P-0611 Field-Wireable Connector - M12 Power Male Connector M12 × 1, Straight





Туре	FW-ERSSM0414-PS-P-0611
ID	100045553
Connector A	Male, M12 × 1, Straight, S-coded
Number of pins	3+PE
Contacts	CuZn, Gold-plated
Contact carriers	Plastic, PA, Black
Connector body	Brass, Nickel-plated, Gray
Coupling nut/screw	Brass, CuZn-Ni, Nickel-plated
External diameter of the cable	611 mm
Core cross-section/Clamping ability	0.752.5 mm²
Connection mode	Push-in connection
Mechanical lifespan	> 100 Mating cycles
Protection class	IP67, (screwed together)
Electrical properties at +20 °C	
Rated voltage	630 V <sub>AC</sub>
Current	16 A
Mechanical and chemical properties	
Ambient temperature (fixed)	-40+85 °C



## **Features**







- ■S coding
- Metal retaining screw
- ■Push-in connection
- ■4-pin (3+PE)
- Cable feedthrough: 6.0...11.0 mm
- ■Shieldable
- Terminal capacity:
  - Max. 1.5 mm² or 16 AWG (without cable end sleeve)
- Max. 2.5 mm² or 14 AWG (without cable end sleeve)

## Contact assignment

