

TX100 HMI Series

4" Display with TX VisuPro Runtime

High-Quality Plastic Housing with a Resistive Touch Screen








TX104P-00VPST

Type	TX104P-00VPST
ID	100049014
Display/touch	
Display	TFT colour
Touchscreen	Resistive, Plastic film front
Active screen area	4.3"
Resolution (pixels)	480 × 272 pixels WQVGA
Format	16:9
Brightness	200 cd/m² typ.
dimmmable	Yes
Controller	
Processor	ARM Cortex A8, 1 GHz
Memory	4 GB Flash
RAM memory	512 MB
Add-on memory	1 x USB host port
Interfaces	
Onboard	1 x RJ45 Ethernet, 1 x RS232/485/422, 1 x USB host, 1 x power supply
Ethernet	1 x 10/100 Mbit
USB	1 × host port
Serial	RS232 / RS485 / RS422
Power supply	
Rated value	24 VDC, max. 0.25 A
Admissible voltage range	10...32 VDC
General data	
Operating ambient conditions	0...50 °C, 5...85 % rel. humidity, non-condensing
Storage ambient conditions	-20...70 °C, 5...85 % rel. humidity, non-condensing
Approvals	CE cULus
Ex approval	Haz. Loc. Class I, Division 2, Groups A, B, C and D
Protection class	IP66 front, IP20 rear NEMA type: 2/4X
Dimensions	
Front (W x H x D)	147 x 107 x 34 mm
Cut-out (W x H)	136 x 96 mm
Mounting depth	29+5 mm
Weight	approx. 0.4 kg



- 4.3" TFT wide screen color display
- LED backlight
- 480 x 272 pixel resolution
- 64 K colors
- Resistive touch screen
- 1 RJ45 Ethernet port
- 1 serial interface (RS232, RS485, RS422)
- 1 USB host port

Connection and pin assignment

	Power Supply The power supply connector is delivered with each device. It can be reordered at Turck as accessories. Type designation: TX-Mount-xx	Pin Assignment 
	USB Interfaces	Pin Assignment 
	Ethernet Ports The Ethernet ports are connected to each other via an internal switch. Ethernet cables (examples): RJ45 male connector – RJ45 male connector: RJ45S-RJ45S-4414-2M (order number: 6441423) RJ45 male connector – M12 male connector, 4-pin, D-coded: RSSD-RJ45S-4414-2M (order number: 6441413) RJ45 male connector – M8 male connector, 4-pin: PSGS4M-RJ45S-4414-2M (order number: 6933005) RJ45 male connector – M12 female receptacle, 4-pin, D-coded: RJ45-FKSDD-4414-2M (order number: 6935282)	Pin Assignment 
	Serial Interface The serial interface can be operated either as RS232, RS485 or RS422. The adjacent wiring diagrams show the respective pin assignments. Attention: In the RS485 mode, pins 3 and 4 as well as 7 and 8 must be externally connected!	Pin Assignment in RS232 Operating Mode  Pin Assignment in RS485 Operating Mode  Pin Assignment in RS422 Operating Mode 

Accessories

Type code	Ident no.		Dimension drawing
TX100-MOUNT-07	100003186	TX100 mounting bracket and power connectors for 4–7" devices	

Function accessories

Type code	Ident no.		Dimension drawing
TX-PSC	100002938	Power Supply Male Connector for TX HMI Devices	