


DW3000-110-PA-H1441
Draw-Wire



Technical data


Type	DW3000-110-PA-H1441
ID	1544548
General data	
Measuring range	3000 mm
Linearity deviation	≤ 0.1 %
Electrical data	
Operating voltage U _B	0...30 VDC
Short-circuit protection	yes
Wire break/reverse polarity protection	yes
Output function	4-pin, Potentiometer
Mechanical data	
Design	Draw Wire
Housing material	Titanium anodized aluminium
min. extension force	6.9 N
max.extension force	9.8 N
max. extension speed	10 m/s
Pull acceleration max.	140 m/s ²
wire material	Stainless steel
Electrical connection	Connector, M12 × 1
Environmental conditions	
Ambient temperature	-20...+85 °C
Protection class	IP65

Signal	+U _B	Slider	Gnd	-	-	-	-	-	-
Pin configuration	1	2	3	4	-	-	-	-	-

Features

- Measuring range up to 3000mm
- M12 connector
- Protection class: IP65 (Encoder)
- Potentiometric output 1k Ohm
- Supply voltage max. 30 VDC

Wiring diagram



Accessories

RDR-1

1544753

Deflection roller for aluminium draw-wire sensors

