

LEDILA290XD6-XQ

Vision System – Linear Area Light



Technical data

Type	LEDILA290XD6-XQ
ID	3014950
Signal and display data	
Purpose	Image processing
Function	Linear light
Light type	IR
Wavelength	850...940 nm
Beam angle	6.5°
LED service life (L70)	50000 h
Special features	Wash down
Electrical data	
Operating voltage U _B	24 VDC
DC rated operating current I _e	≤ 1000 mA
Max. current consumption per color	1000 mA
Mechanical data	
Design	Rectangular
Dimensions	332.6 x 59.4 x 32.6 mm
Housing material	Metal, Anodized AL
Window material	Plastic, diffuse
Electrical connection	Connector, M12 × 1, PVC
Number of cores	5
Ambient temperature	0...+50 °C
Protection class	IP50
Tests/approvals	
Approvals	CE, cULus listed

Features

- High-Intensity
- Protection class: IP50
- Color: infrared
- Power supply: 24 VDC
- M12 x 1 male

Wiring diagram



Functional principle

High-intense illumination of large areas at long distances.