

EA5E750Q Measuring Light Screen – Emitter



Technical data

Туре	EA5E750Q	
ID	3075427	
Optical data		
Function	Light screen	
Operating mode	Emitter	
Light type	IR	
Optical resolution	5 mm	
Range	4004000 mm	
Scan field	750 mm	
Number of beams	150	
Electrical data		
Operating voltage	1230 VDC	
No-load current	≤ 400 mA	
Readiness delay	≤ 2 s	
Blanking function	yes	
Mechanical data		
Design	Rectangular, EZ-Array	
Dimensions	45.2 x 36 x 828 mm	
Housing material	Metal, AL, Anodized	
Lens	plastic, Acrylic	
Electrical connection	Connector, M12 × 1	
Ambient temperature	-40+70 °C	
Protection class	IP65	
Power-on indication	LED, Red	
Error indication	Flashing	
Tests/approvals		
Approvals	CE	



Features

Male M12 × 1, 8-pin Scan field 750 mm

Protection class IP65

Resolution 5 mm

Max. range 4 m

■2 × EZA-MBK-11 brackets included in deliv-

ery
Operating voltage 12...30 VDC

Wiring diagram



Functional principle

The measuring light screen EZ-Array is ideal for sizing and product profiling, edge and centre guiding, sag and hole detection as well as parts counting. The two-part light screen is easily installed. The electronics is incorporated in the receiver housing and can be configured via 6 DIP switches. For special functions, the screen can be adjusted via PC with the enclosed software. To synchronize emitter and receiver just interconnect the sync-outputs of both.



Accessories



3071470 Mounting bracket, steel, blackfinished, for EZ-ARRAY and EZ-SCREEN standard and cascade 14 & 30 mm



3071756

Mounting bracket, steel, blackfinished, for EZ-ARRAY and EZ-SCREEN standard and cascade 14 & 30 mm



3072587 Mounting bracket, steel, blackfinished, for EZ-ARRAY and EZ-SCREEN standard 14 & 30 mm

Accessories

Dimension drawing	Туре	ID	
	RKS8T-2/TEL	6625446	Connection cable, M12 female connector, straight, 8-pin, cable length: 2 m, sheath material: PVC, black; shielded; cULus approval; other cable lengths and qualities available, see www.turck.com
0 15 M12x1 ∞ 14 0 37.5 → 0 50 →	WKS8T-2/TXL	6625461	Connection cable, M12 female connector, angled, 8-pin shielded, cable length: 2 m, jacket material: PUR, black; cULus approval; other cable lengths and qualities available, see www.turck.com
M12x1 0 15 5 14	RKC8T-2/TEL	6625130	Connection cable, M12 female, straight, 8-pin, cable length: 2 m, jacket material: PVC, black; cULus approval; other cable lengths and qualities available, see www.turck.com
0 15 14 26.5 32 	WKC8T-2/TEL	6625133	Connection cable, M12 female connector, angled, 8-pin, cable length: 2 m, jacket material: PVC, black; cULus approval; other cable lengths and qualities available, see www.turck.com



