

DS18VP6LPQ8

Photoelectric Sensor

Technical data

Type	DS18VP6LPQ8
ID	3076552
Optical data	
Function	Retroreflective Sensor
Operating mode	Polarized
Wavelength	660 nm
Range	5...3500 mm
Electrical data	
Operating voltage	10...30 VDC
Residual ripple	< 10 % U _{ss}
DC rated operational current	≤ 100 mA
Short-circuit protection	yes
Reverse polarity protection	yes
Output function	NO/NC, PNP
Current output	100 mA
Readiness delay	≤ 100 ms
Response time typical	< 2 ms
Mechanical data	
Design	Rectangular with thread, DS18
Dimensions	Ø 18 x 31.1 x 15 x 59.9 mm
Housing material	Plastic, Thermoplastic material
Lens	Acrylic
Electrical connection	Connector, M12 × 1, PVC
Number of cores	4
Ambient temperature	-20...+70 °C
Protection class	IP67
Switching state	LED, Yellow
Error indication	LED, green, Flashing
Excess gain indication	LED, yellow, flashing
Tests/approvals	



Features

- Operating voltage: 10...30 VDC
- PNP switching output, changeover

Wiring diagram

