

Photoelectric Sensor DS18VP6LPW W/30

Type	DS18VP6LPW W/30
ID	3076758
Optical data	
Function	Retroreflective Sensor
Operating mode	Polarized
Wavelength	660 nm
Range	5...3000 mm
Electrical data	
Operating voltage U_s	10...30 VDC
Residual ripple	< 10 % U_s
DC rated operating current I_s	≤ 100 mA
Short-circuit protection	yes
Reverse polarity protection	yes
Output function	NO/NC, PNP
Readiness delay	≤ 100 ms
Response time typical	< 2 ms
Mechanical data	
Design	Rectangular with thread, DS18
Dimensions	Ø 18 x 31.1 x 15 x 47.9 mm
Housing material	Plastic, Thermoplastic material
Electrical connection	Cable, 9 m, PVC
Number of cores	4
Ambient temperature	-20...+70 °C
Protection class	IP67
Switching state	
Switching state	LED, Yellow
Error indication	LED, green, Flashing
Excess gain indication	LED, yellow, flashing
Tests/approvals	



- Operating voltage: 10...30 VDC
- PNP switching output, changeover

Wiring Diagram

