


AD-MFS4-FKM4.4

Adapter



Technical data


Type	AD-MFS4-FKM4.4
ID	6634969
Connector A	Male, M8 × 1, Straight
Number of pins	4
Contacts	Brass, CuZn, Gold-plated
Contact carriers	Plastic, TPU, Black
Connector body	Plastic, TPU, Black
Coupling nut/screw	Brass, CuZn, Nickel-plated
Tightening torque (range)	0.5 ... 0.6 Nm (observe max. torque of mating connector!)
Mechanical lifespan	> 100 Mating cycles
Protection class	IP67, (screwed together)
Connector B	Female, M12 × 1, Straight
Number of Pins	4
Contacts	Brass, CuZn, Gold-plated
Contact carriers	Plastic, TPU, Black
Connector body	Plastic, TPU, Black
Coupling nut/retaining screw	Brass, CuZn, Nickel-plated
Tightening torque	0.6 ... 0.8 Nm (observe max. torque of mating connector!)
Mechanical life	> 100 Mating cycles
Protection class	IP67, (Screwed together)
Electrical properties at +20 °C	
Rated voltage	60 V
Current	4 A

Features




- M12 female connector — M8 male connector, 4-pin
- RoHS compliant
- Protection class: IP67

Contact assignment



Circuit Diagram



Technical data

Mechanical and chemical properties

Ambient temperature (fixed)	-30...+80 °C
-----------------------------	--------------
