


Accessories Protective housing SG-DSU35TC



Туре	SG-DSU35TC
ID	6900437
Design	Accessories for dual sensor, Ni4-DSU35
Dimensions	104 x 86 x 38.5 mm
Housing material	Stainless steel, 1.4401 (AISI 316)

- Robust stainless steel housing for model DSU35 dual sensors
- For mechanically protected mounting
- Also for protecting against UV radiation and damage to DSU35 model sensors in ATEX dust and gas zones
- Openings for LEDs
- Removable cover for access to the terminal chamber or connectors of mounted sensors

General description

If dual sensors of the series DSU35 are applied in Ex-areas, mechanical protection of the installation may be obligatory. Correct installation of the protective housing fulfills this requirement.

Mounting:

The lower part of the housing is placed between the rotary actuator and dual sensor, and fixed via the M5 screws, which come with the actuating element (puck). The upper cover is mounted onto the bottom half of the housing with the delivered M5 hexagon socket screws.

