



B5131-0
Field-Wireable Connector
Female Connector M8 × 1/Ø 8 mm, Straight



Technical data

Type	B5131-0
ID	6904910
Connector A	Female, M8 × 1, Straight
Number of pins	3
Contacts	Bronze, CuSn, Gold-plated
Contact carriers	Plastic, PA, Black
Connector body	Plastic, PBT, Black
Coupling nut/screw	Die-cast Zinc, GD-Zn, Nickel-plated
Seal	Plastic, Neoprene
Screw-in thread seal	Plastic
Screw-in thread	M11 × 0.75
External diameter of the cable	3.5...5 mm
Core cross-section/Clamping ability	0.14...0.25 mm²
Connection mode	Solder contact
Protection class	IP67, (screwed together)
Electrical properties at +20 °C	
Rated voltage	60 V
Current	4 A
forward resistance	≤ 3 mΩ
Mechanical and chemical properties	
Ambient temperature (fixed)	-40...+85 °C
Approvals	cULus recognized

Features



- Metal coupling nut
- Protection class IP67
- Lötanschluss
- Field-wireable female connector
- Mechanical connection M8/Ø 8 mm
- Straight design
- 3-pin
- metr. Screw-in thread M11 × 0.75
- Cable feedthrough 3.5...5.0 mm

Contact assignment

