

piconet Accessories PICONET-SET-M12



- 10 label clips 5 × 10
- IP67: 5 M12 dummy plugs, 2 photoelectric dummy plugs
- Dust caps: 2 M8 caps, 1 M12 cap

Type	PICONET-SET-M12
ID	8015078
Vibration test	Acc. to EN 60068-2-6
Shock test	acc. to DIN EN 60068-2-27
Electromagnetic compatibility	Acc. to EN 61000-6-2/EN 61000-6-4
Protection class	IP67
Approvals	CE, cULus