


compact fieldbus station for AS-interface


4 Inputs

FAS4-S0400




- Bus connected via AS-interface flat cable or male M12 x 1
- Field devices connected via male M12 x 1
- AS-i specification V2.1
- Short-circuit diagnostics
- Cast housing
- Protection class IP67
- Address range 1...31 A/B
- 4 inputs 3-wire PNP
- 24 VDC

Fieldbus



M12 x 1 Giriş

3-wire pnp sensor



Tip	FAS4-S0400
Tanıt. no.	6821321
Kanal sayısı	4
Operating / load voltage	18...31 VDC (AS-i)
internal power consumption	<20 mA plus I/O supply
Girişler	
Number of channels	4
Düşük seviye sinyal akımı	<2 mA at 24 VDC
Yüksek seviye sinyal akımı	3...3.4 mA at 24 VDC
Giriş gecikmesi	2,5 ms
Maks. giriş akımı	Toplam: 200 mA
Fieldbus adres aralığı	1...31 A/B
Fieldbus adresleme	AS-i addressing tool
LEDs Bus	I/O: green = on AS-i green = OK . red/green = fault
Boyutlar (W x L x H)	60 x 124.7 x 28 mm
Housing material	fibre-glass reinforced Polyamide (PA6-GF30)
Montaj	4 mounting holes Ø 5,4 mm
Ortam sıcaklığı	-25...+70 °C
IP Derecesi	IP67