



DeviceNet için bağımsız piconet modülü 1-channel Incremental Encoder Interface SDNB-10S-0001




- Incremental encoder interface
- 1-channel
- Configuration interface
- Parameterizable functions
- Supported via I/O-ASSISTANT 2
- Direct connection to the fieldbus
- Fibre-glass reinforced housing
- Shock and vibration tested
- Encapsulated module electronics
- Metal connector
- Degree of protection IP67


M12 × 1 Fieldbus




M12 × 1 Kapı/Mandal Girişi



Encoder - M23 × 1



M8 × 1 Güç Besleme



Tip	SDNB-10S-0001
Tanıt. no.	6824094
Kanal sayısı	1
Operating / load voltage	20...29 VDC
Operating current	≤ 55 mA
Fieldbus iletim hızı	125/250/500 kbps
Fieldbus adresleme	0 to 99
Servis arayüzü	parameterisation via I/O-ASSISTANT
Electrical isolation	Fieldbus to operational voltage
Maksimum sınırlama frekansı, analog	1 MHz
Rectangular decoder	1-port, 2-port, 4-port evaluation
Counter	16 bit binary
Actuator power supply	5 VDC
Zero pulse latch	16 bit
Commands	read, set, activate
Boyutlar (W x L x H)	30 x 175 x 26.5 mm
Titreşim testi	EN 60068-2-6 uyarınca
Darbe testi	acc. to DIN EN 60068-2-27
Elektromanyetik uyumluluk	EN 61000-6-2/EN 61000-6-4 uyarınca
IP Derecesi	IP67
Onaylar	CE, cULus