


CANopen için piconet tek başına modülü

1-channel SSI Sensor Interface


SCOB-10S-0005




- SSI encoder interface
- 1-channel
- Configuration interface
- Parameterizable functions
- Supported via I/O-ASSISTANT 2
- Direct connection to the fieldbus
- Fibre-glass reinforced housing
- Shock and vibration tested
- Encapsulated module electronics
- Metal connector
- Degree of protection IP67

Tip	SCOB-10S-0005
Tanıt. no.	6824157
Kanal sayısı	1
Operating / load voltage	20...29 VDC
Operating current	≤ 55 mA
Fieldbus iletim hızı	10 kbps ...1 Mbps
Fieldbus adresleme	0 to 99
Servis arayüzü	parameterisation via I/O-ASSISTANT
Electrical isolation	Fieldbus to operational voltage
Bit transfer	Diferansiyel (RS485)
Transmission rate	variable up to 1 MHz (default 250 Hz)
Serial input	24 bit
Data direction	read
Sensör besleme	24 VDC from load voltage
Potential separation	operating voltage to RS232
Boyutlar (W x L x H)	30 x 175 x 26.5 mm
Titreşim testi	EN 60068-2-6 uyarınca
Darbe testi	acc. to DIN EN 60068-2-27
Elektromanyetik uyumluluk	EN 61000-6-2/EN 61000-6-4 uyarınca
IP Derecesi	IP67
Onaylar	CE, cULus

M12 × 1 Fieldbus



Enkoder - M23 × 1



M8 × 1 Güç Besleme

