



PROFIBUS-DP için piconet tek başına modülü 2-channel Pulse Width Modulation (PWM) SDPB-0002D-1002




- Pulse width modulation
- 2-channel
- 2.5 A per channel
- Configuration interface
- Parameterizable functions
- Supported via I/O-ASSISTANT 2
- Direct connection to the fieldbus
- Fibre-glass reinforced housing
- Shock and vibration tested
- Encapsulated module electronics
- Metal connector
- Degree of protection IP67

Tip	SDPB-0002D-1002
Tanıt. no.	6824437
Kanal sayısı	2
Operating / load voltage	20...29 VDC
Operating current	≤ 25 mA
Fieldbus iletim hızı	9.6 kbps ...12 Mbps
Fieldbus adresleme	0 to 99
Servis arayüzü	parameterisation via I/O-ASSISTANT
Electrical isolation	Fieldbus to operational voltage
V/R output	0,5 A, kısa devre korumalı
Kanal başına çıkış akımı	2.5
Yük tipi	resistive, inductive
Base frequency	1 Hz...10 kHz (default 250 Hz)
Duty factor	0...100 % (t ON > 750 ns, t OFF > 500 ns)
Çözünürlük	10 Bit
Freewheeling diode	on the outputs
Boyutlar (W x L x H)	30 x 210 x 26.5 mm
Titreşim testi	EN 60068-2-6 uyarınca
Darbe testi	acc. to DIN EN 60068-2-27
Elektromanyetik uyumluluk	EN 61000-6-2/EN 61000-6-4 uyarınca
IP Derecesi	IP67
Onaylar	CE, cULus


M12 × 1 Fieldbus



M12 × 1 Çıkış



M8 × 1 Güç Besleme



Data in process image

	Address	Input data		Output data	
Pre-conditions	Word	High-Byte	Low-Byte	High-Byte	Low-Byte
Complex mapping: Data are mapped with control and status byte	0	Ch0 Reg1	SB0	Ch0 D1	CB0
	1	SB1	Ch0 Reg0	CB1	Ch0 D0
	2	Ch1 Reg0	Ch1 Reg1	Ch1 D0	Ch1 D1