

IO-Link Starterkit

IO-Link Starterkit

Typ	IO-Link Starterkit
ID č.	100012813

Součást dodávky	<p>Carrying case, black/yellow □ Bottom lining, black, 248 x 182 x 33 mm, account assigned □ Cover profile foam, black, 248 x 182 x 21 mm 1:2 □ Plug-in power supply, 24 VDC 0.5 A Type 512692 — NA with M8 female connector □ 8-GB USB stick with software set □ IO-Link master TBEN-S2-4IOL (6814024) □ Ethernet cable PSGS4M-RJ45S-4414-1M (6933004) □ Connection cable RKC4T-2-RSC4T/TXL (6625604) □ I/O hub TBIL-S4-8DXP (100002596) □ Inductive sensor BI10U-M18-IOL6X2-H1141 (1644875) □ Ultrasonic sensor RU40U-M18M-AP8X2-H1151 (1610094) □ Indicator light K50L2RGBKQ (3802158)</p>
-----------------	---



- Kompletní sada obsahující IO-Link master, senzory IO-Link, I/O hub, parametrizační software a příslušenství.
- obsahuje napájení 230 VAC/24 VDC

Function accessories

Typové označení	Identifikační číslo		Rozměrový náčrtek
RU40U-M18M-AP8X2-H1151/P0001	100032174	Ultrazvukový senzor, závitové pouzdro 18 mm, niklovaná mosaz	