

# STP-M12D-415

## Extension Cable – Ethernet Cable

Keine Maßzeichnung  
vorhanden!

No drawing available!

### Features

- M12 × 1 female connector, straight, 4-pin, D-coded
- Grip: PUR, black
- Coupling nut: nickel-plated brass
- RJ45 male connector, 8-pin
- Gold-plated contacts, 8 × 24 AWG
- Cable diameter: 6.20 mm
- Cable jacket: PUR, green
- Protection class IP67
- Temperature range: -40...+70 °C
- Rated voltage: 50 VDC/VAC
- Ampacity: 2 A
- Shielded
- Cable length: 4.57 m

### Technical data

Type	STP-M12D-415
ID	3806415
Electrical connection	4.57 m