

**TURCK****Hans Turck GmbH & Co. KG**

Witzlebenstr. 7 | 45472 Mülheim an der Ruhr, Germany  
 T +49 208 4952-0 | F +49 208 4952-264

Company / customer

Project description

Drawing number ID 100003097; EG-VA655526/111-0212/2GD60

Commission

Manufacturer (company)

Hans Turck GmbH &amp; Co. KG

Manufacturer (company)

Path

Path

Project name

ID 100003097\_V2

Protection class

Make

Power supply

Type

Supply line

Place of installation

Control voltage

Responsible for project

Hans Turck GmbH &amp; Co. KG

Part feature

Year of manufacture

Created on 26.10.2018

Edit date 15.12.2020 by (short name) Bast

Number of pages 13

			Date	26.10.2018			Cover Sheet		=		
			Ed.	Himanshu.Singh					+ EXCOM_RIO		
			Appr.								
Modification	Date	Name	Original		Replacement of	Replaced by		ID 100003097; EG-VA655526/111-0212/2GD60	Page	1	
									Page	1	



# Parts list


SR. NO.	DEVICE TAG	QTY.	PART DESCRIPTION	MANUFACTURER	PART NUMBER	TYPE NUMBER
1	-CABINET_BASE	1	Cabinet (650 x 550 x 260)	ROSE Systemtechnik GmbH	ROSE.A20672	A20672
2	-CABINET_DOOR	1	Door with Window (650 x 550 x 260)	ROSE Systemtechnik GmbH	ROSE.A20674	A20674
3	-FLANGE	1	Flange for ROSE cabinet 650x550x260	ROSE Systemtechnik GmbH	ROSE.FLANGE_65XX26_1X1_V2	FLANGE_65XX26_1X1_V2
4	-FLANGE_BREATHER	1	M20 Breather/Drainer with stainless steel castled nut	Redapt	RED.DP-E-4-0-04-S3	DP-E-4-0-04-S3
5	-FLANGE_GLAND_M16_BU	96	PU Gland Ex-e Blue M16	WISKA Hoppmann GmbH	WISKA.ESKE/1-i 16	ESKE/1-i 16
6	-FLANGE_GLAND_M20_BU	4	PU Gland Ex-e Blue M20	WISKA Hoppmann GmbH	WISKA.ESKE/1-i 20	ESKE/1-i 20
7	-FLANGE_GLAND_M25_BK	4	PU Gland Ex-e Black M25	WISKA Hoppmann GmbH	WISKA.ESKE/1-e 25	ESKE/1-e 25
8	-MT	1	Remote I/O System excom® Module rack, zone 1, for 16 modules	Hans Turck GmbH	TUR.9100687	MT16-2G
9	-MT_GW1	1	Sub-D Connector (for Ex I PROFIBUS devices)	Hans Turck GmbH	TUR.6890944	D9T-RS485 IS
10	-MT_GW2	1	Sub-D Connector (for Ex I PROFIBUS devices)	Hans Turck GmbH	TUR.6890944	D9T-RS485 IS
11	-OC1	1	Remote I/O System excom® PROFIBUS-DP fiber-optic coupler for zone 1	Hans Turck GmbH	TUR.6890427	OC11Ex/2G.2
12	-OC1_BUS	1	Sub-D Connector (for Ex I PROFIBUS devices)	Hans Turck GmbH	TUR.6890944	D9T-RS485 IS
13	-OC2	1	Remote I/O System excom® PROFIBUS-DP fiber-optic coupler for zone 1	Hans Turck GmbH	TUR.6890427	OC11Ex/2G.2
14	-OC2_BUS	1	Sub-D Connector (for Ex I PROFIBUS devices)	Hans Turck GmbH	TUR.6890944	D9T-RS485 IS
15	-PPS	1	Remote I/O System excom® Upstream subrack for PPSA	Hans Turck GmbH	TUR.9100516	MT-PPS
16	-X	2	End bracket	PHOENIX CONTACT	PXC.3022276	CLIPFIX 35-5
17	-X1	2	Feed-through terminal block	PHOENIX CONTACT	PXC.3044160	UT 10
18	-X1	2	Feed-through terminal block	PHOENIX CONTACT	PXC.3044188	UT 10 BU

2



4

Date	15.12.2020		Parts List	= + EXCOM_RIO	ID 100003097; EG-VA655526/111-0212/2GD60	Page	3
Ed.	Bast					Page	
Appr						Page	
Modification	Date	Name	Original	Replacement of	Replaced by		







DOOR VIEW



RIGHT VIEW





MOUNTING VIEW



LEFT VIEW

















			Date	31.10.2018		24VDC Distribution	= + EXCOM_RIO	ID 100003097; EG-VA655526/111-0212/2GD60	Page	10
			Ed.	Himanshu.Singh					Page	10
			Appr							
Modification	Date	Name	Original		Replacement of	Replaced by				



			Date	31.10.2018	<b>TURCK</b>	MT PWR Wiring	=	+ EXCOM_RIO	ID 100003097; EG-VA655526/111-0212/2GD60	Page	11
			Ed.	Himanshu.Singh						Page	11
			Appr								
Modification	Date	Name	Original		Replacement of	Replaced by					



			Date	31.10.2018	<b>TURCK</b>	OC1 Wiring			=	
			Ed.	Himanshu.Singh					+ EXCOM_RIO	
			Appr							
Modification	Date	Name	Original		Replacement of	Replaced by	ID 100003097; EG-VA655526/111-0212/2GD60		Page 12	
									Page	



			Date	31.10.2018	<b>TURCK</b>	OC2 Wiring	=	+ EXCOM_RIO	ID 100003097; EG-VA655526/111-0212/2GD60	Page	13
			Ed.	Himanshu.Singh						Page	13
			Appr							Page	13
Modification	Date	Name	Original		Replacement of	Replaced by					