

**TURCK**

Hans Turck GmbH &amp; Co. KG

Witzlebenstr. 7 | 45472 Mülheim an der Ruhr, Germany

T +49 208 4952-0 | F +49 208 4952-264

Company / customer

Project description

Drawing number ID 100003098; EG-VA655526/112-0212/2GD60

Commission

Manufacturer (company)

Hans Turck GmbH &amp; Co. KG

Manufacturer (company)

Path

Path

Project name

ID 100003098\_V2

Protection class

Make

Power supply

Type

Supply line

Place of installation

Control voltage

Responsible for project

Hans Turck GmbH &amp; Co. KG

Part feature

Year of manufacture

Created on 26.10.2018

Edit date 15.12.2020 by (short name) Bast

Number of pages 13

			Date	26.10.2018			Cover Sheet		=	
			Ed.	Shradha.Waknis				+ EXCOM_RIO		
			Appr							
Modification	Date	Name	Original		Replacement of	Replaced by		ID 100003098; EG-VA655526/112-0212/2GD60	Page	1
									Page	1



# Parts list


SR. NO.	DEVICE TAG	QTY.	PART DESCRIPTION	MANUFACTURER	PART NUMBER	TYPE NUMBER
1	-CABINET_BASE	1	Cabinet (650 x 550 x 260)	ROSE Systemtechnik GmbH	ROSE.A20672	A20672
2	-CABINET_DOOR	1	Door with Window (650 x 550 x 260)	ROSE Systemtechnik GmbH	ROSE.A20674	A20674
3	-FLANGE	1	Flange for ROSE cabinet 650x550x260	ROSE Systemtechnik GmbH	ROSE.FLANGE_65XX26_1X2_V2	FLANGE_65XX26_1X2_V2
4	-FLANGE_BREATHER	1	M20 Breather/Drainer with stainless steel castled nut	Redapt	RED.DP-E-4-0-04-S3	DP-E-4-0-04-S3
5	-FLANGE_GLAND_M20_BU	100	PU Gland Ex-e Blue M20	WISKA Hoppmann GmbH	WISKA.ESKE/1-i 20	ESKE/1-i 20
6	-FLANGE_GLAND_M25_BK	4	PU Gland Ex-e Black M25	WISKA Hoppmann GmbH	WISKA.ESKE/1-e 25	ESKE/1-e 25
7	-MT	1	Remote I/O System excom® Module rack, zone 1, for 16 modules	Hans Turck GmbH	TUR.9100687	MT16-2G
8	-MT_GW1	1	Sub-D Connector (for Ex I PROFIBUS devices)	Hans Turck GmbH	TUR.6890944	D9T-RS485 IS
9	-MT_GW2	1	Sub-D Connector (for Ex I PROFIBUS devices)	Hans Turck GmbH	TUR.6890944	D9T-RS485 IS
10	-OC1	1	Remote I/O System excom® PROFIBUS-DP fiber-optic coupler for zone 1	Hans Turck GmbH	TUR.6890427	OC11Ex/2G.2
11	-OC1_BUS	1	Sub-D Connector (for Ex I PROFIBUS devices)	Hans Turck GmbH	TUR.6890944	D9T-RS485 IS
12	-OC2	1	Remote I/O System excom® PROFIBUS-DP fiber-optic coupler for zone 1	Hans Turck GmbH	TUR.6890427	OC11Ex/2G.2
13	-OC2_BUS	1	Sub-D Connector (for Ex I PROFIBUS devices)	Hans Turck GmbH	TUR.6890944	D9T-RS485 IS
14	-PPS	1	Remote I/O System excom® Upstream subrack for PPSA	Hans Turck GmbH	TUR.9100516	MT-PPS
15	-X	2	End bracket	PHOENIX CONTACT	PXC.3022276	CLIPFIX 35-5
16	-X1	2	Feed-through terminal block	PHOENIX CONTACT	PXC.3044160	UT 10
17	-X1	2	Feed-through terminal block	PHOENIX CONTACT	PXC.3044188	UT 10 BU
18	-X1	2	Ground modular terminal block	PHOENIX CONTACT	PXC.3044173	UT 10-PE

2



4

			Date	15.12.2020		Parts List			=
			Ed.	Bast					+ EXCOM_RIO
			Appr						
Modification	Date	Name	Original		Replacement of	Replaced by	ID 100003098; EG-VA655526/112-0212/2GD60		Page 3
								Page	4






DOOR VIEW



RIGHT VIEW




MOUNTING VIEW




LEFT VIEW






			Date	15.12.2020			<b>TURCK</b>	GA Mounting					
			Ed.	Bast									
			Appr										
Modification	Date	Name	Original	Replacement of	Replaced by					ID 100003098; EG-VA655526/112-0212/2GD60		Page	7
												Page	8










			Date	26.10.2018		24VDC Distribution	= + EXCOM_RIO	ID 100003098; EG-VA655526/112-0212/2GD60	Page	10
			Ed.	Shradha.Waknis					Page	10
			Appr							
Modification	Date	Name	Original		Replacement of	Replaced by				







			Date	31.10.2018	<b>TURCK</b>	OC2 Wiring	=	+ EXCOM_RIO	ID 100003098; EG-VA655526/112-0212/2GD60	Page	13
			Ed.	Shradha.Waknis						Page	13
			Appr							Page	13
Modification	Date	Name	Original		Replacement of	Replaced by					