


# P4OI-BC

## 视觉系统 – 带有集成分析功能的照相机



### 技术数据


|            |                                                          |
|------------|----------------------------------------------------------|
| 型号         | P4OI-BC                                                  |
| 货号         | 3075397                                                  |
| 相机数据       |                                                          |
| 功能         | 多功能                                                      |
| Resolution | 752 × 480 像素                                             |
| 电气数据       |                                                          |
| 工作电压       | 10...30 VDC                                              |
| 直流额定工作电流   | ≤ 550 mA                                                 |
| 通信协议       | EtherNet/IP<br>Modbus TCP<br>Modbus TCP<br>PCCC<br>RS232 |
| 输出性能       | 常开触点, PNP/NPN                                            |
| 通电显示       | LED指示灯, 绿                                                |
| 开关状态指示     | LED指示灯, 绿                                                |
| 故障显示       | LED指示灯, 红                                                |
| 机械数据       |                                                          |
| 设计         | 内联, P4                                                   |
| 尺寸         | 136.1 x 66.8 x 34.3 mm                                   |
| 外壳材料       | 金属, 铝                                                    |
| 电气连接       | 接插件, M12 × 1, 12线                                        |
| 工作温度       | 0...+50 °C                                               |
| 防护等级       | IP20                                                     |
| 测试/认证      |                                                          |
| 认证         | CE                                                       |



### 特点

- 全部功能, AREA, EDGE / GEO
- 1/3" CMOS, 752x480 像素
- RGB- / HSI 颜色空间
- 一体式设计, 摄像头和集成控制器
- 镜头垂直连接到产品纵轴
- 防护等级IP20
- 分离式镜头
- 工作电压:12针M12针头接插件, 10...30 VDC
- 外部触发输入
- 外部选通输出3 针M8
- EtherNet/IP 和 Modbus TCP RJ45接口
- RS232数据通讯
- 轴向BNC视频连接电缆

### 接线图



### 功能原理

The camera system PresencePLUS P4 consists of a camera with an integrated processing unit. Lens, lighting and connection cable are to be ordered separately. Freeware and firmware updates are available for download on: [www.bannerengineering.com](http://www.bannerengineering.com)

附件

| 尺寸图 | 型号    | 货号      |                         |
|-----|-------|---------|-------------------------|
|     | P4C06 | 3073491 | 供电，M12孔头，12针，1.83m      |
|     | BNC06 | 3067458 | 轴向BNC连接电缆，1.83米         |
|     | STP07 | 3069985 | RJ45 Ethernet数据线, 2.13m |