

## Handheld with Lithium-Ion Battery PD-IDENT-UHF-RBTW-920-925



- Mobile reading and writing of RFID tags
- Handheld with UHF antenna
- Microsoft Windows CE 5
- Incl. TURCK RFID TW-UHF software for reading and writing of data
- Customized software solution on request
- Bluetooth
- Protection class IP65
- Withstands multiple drops on concrete from 1.5 m height
- Incl. docking station with power supply, USB cable
- Optionally available on request: Barcode scanner (1D / 2D imager or 1D laser)
- Optionally available on request: WLAN and software development kit (SDK)

<b>Type</b>	PD-IDENT-UHF-RBTW-920-925
<b>ID</b>	7030532
<b>Ambient temperature</b>	-20...+50 °C
<b>Storage temperature</b>	-40...+60 °C
<b>Electrical data</b>	
Data transfer	Alternating electromagnetic field
Operating frequency	920...925 MHz
Radio communication and protocol standards	ISO 18000-63 EPCglobal Gen 2
Output power	500 mW (ERP), adjustable
Antenna polarization	linear horizontal
<b>Device features</b>	
Memory	XScale, 624 MHz
Display	1-GB flash ROM; 256-MB RAM
Keyboard	3.7, 640 × 480 pixels, Touchscreen
Battery capacity	55 Keys
Communication via	3300 mAh
Included software	Bluetooth Class II
Operating system	Turck RFID software, SDK available as free download
Docking station connection type	WinCE
	USB (serial)
<b>Mechanical data</b>	
Dimensions	260x 100x 42mm
Housing material	Plastic, Black
<b>Protection class</b>	IP65

## Handheld with Lithium-Ion Battery

### PD-IDENT-UHF-RBTW-920-925

#### Accessories

Type code	Ident no.		Dimension drawing
PD-IDENT-TA-RS232	7030554	RS232 adapter cable for direct connection of the TA handhelds to a device with RS232-interface (e.g. PLC, PC)	
PD-IDENT-TW-3300	7030517	Replacement battery 3300 mAh	
PD-IDENT-TA-STYLUS	7030550	replacement pens (5 pcs.)	
PD-IDENT-TA-STYLUS-HOLDER-KIT	7030549	Stylus with holder (only usable without pistol grip)	
PD-IDENT-TA-POUCH	7030548	Carrying case for the TW and TA handhelds without pistol grip	
PD-IDENT-TA-DOCK	7030596	Docking station, incl. power supply unit	
PD-IDENT-TA-POWERSUPPLY	7030597	Power supply unit	