

Your Global Automation Partner

TURCK

BI/NI-IOLU69X2-H1141

Inductive Sensors

IO-Link Parameters – IO-Link Version 1.1



Contents

1	About This Manual	5
1.1	Target groups.....	5
1.2	Explanation of symbols used	5
1.3	Other documents	5
1.4	Feedback about these instructions.....	5
2	Notes on the Product	6
2.1	Product identification.....	6
2.2	Manufacturer and service	6
3	Software-Supported IO-Link Parameterization.....	7
4	IO-Link Parameters.....	8
4.1	General parameters	8
4.2	Process input data.....	9
4.3	Standard parameters.....	10
4.4	Parameters.....	12

1 About This Manual

This manual describes the parameterization of devices using IO-Link. The manual contains general information on IO-Link and a list of the available parameters.

1.1 Target groups

These instructions are aimed a qualified personal and must be carefully read by anyone mounting, commissioning, operating, maintaining, dismantling or disposing of the device.

1.2 Explanation of symbols used

The following symbols are used in these instructions:



DANGER

DANGER indicates a dangerous situation with high risk of death or severe injury if not avoided.



WARNING

WARNING indicates a dangerous situation with medium risk of death or severe injury if not avoided.



CAUTION

CAUTION indicates a dangerous situation of medium risk which may result in minor or moderate injury if not avoided.



NOTICE

NOTICE indicates a situation which may lead to property damage if not avoided.



NOTE

NOTE indicates tips, recommendations and useful information on specific actions and facts. The notes simplify your work and help you to avoid additional work.



CALL TO ACTION

This symbol denotes actions that the user must carry out.



RESULTS OF ACTION

This symbol denotes relevant results of actions.

1.3 Other documents

Besides this document the following material can be found on the Internet at www.turck.com:

- Data sheet
- Instructions for use


1.4 Feedback about these instructions

We make every effort to ensure that these instructions are as informative and as clear as possible. If you have any suggestions for improving the design or if some information is missing in the document, please send your suggestions to techdoc@turck.com.

2 Notes on the Product

2.1 Product identification

B I 5 - M18 - IOL U 69 X2 - H 1 4 1



2.2 Manufacturer and service

Hans Turck GmbH & Co. KG
 Witzlebenstraße 7
 45472 Muelheim an der Ruhr
 Germany

Turck supports you with your projects, from initial analysis to the commissioning of your application. The Turck product database contains software tools for programming, configuration or commissioning, data sheets and CAD files in numerous export formats. You can access the product database at the following address: www.turck.de/products
 For further inquiries in Germany contact the Sales and Service Team on:

- Sales: +49 208 4952-380
- Technology: +49 208 4952-390

Outside Germany, please contact your local Turck representative.

3 Software-Supported IO-Link Parameterization

The ports of the IO-Link master can be configured in IO-Link mode (IOL) or in Standard IO mode (SIO).

If a port is set to SIO mode, the IO-Link master at this port behaves like a normal digital input. The connected IO-Link device transfers its conventional switching output to the IO-Link master – no communication takes place between the device and the IO-Link master.

If the port is configured in IOL mode, the IO-Link master tries to wake the connected IO-Link device via the "Wake-up Request". If the master receives a response from the IO-Link device, both devices start to communicate with each other. The communication parameters are exchanged first of all; the cyclic data exchange of the process data (process data objects) then starts.

When IO-Link communication (IOL mode) is active, both a cyclic and acyclic communication service is available.

There are two ways of setting the parameters via IO-Link:

- via on-request data objects (e.g. close to the PLC via IO-Link function block)
- via tool-based engineering via FDT/DTM (e.g. PACTware with the use of DTM or the IODD)

Device parameters (on-request data objects)

Device parameters are exchanged acyclically and on request of the IO-Link master. The IO-Link master always sends a request to the device first, then the device responds. This applies when the data is written into the device and also when read from the device. On-request data objects (ORDO) enable parameter values to be written into the device (write) or device states to be read from the device (read).

IO-Link configuration in PROFINET

Using SIDI (Simple IO-Link Device Integration), IO-Link devices can be configured in PROFINET applications directly in the programming environment (e.g. TIA Portal). The Turck IO-Link devices are integrated in the GSDML file of the IO-Link masters in the TBEN, TBPN and FEN20 product series and can be configured in the programming environment as submodules of a modular I/O system. During this process, the user has access to all device properties and parameters.

4 IO-Link Parameters

4.1 General parameters

Parameter	Content
Vendor ID	317 (0x13D)
Device ID	852225 (0xD0101)
IO-Link version	1.1
Bitrate	COM2 (38.4 kbit/s)
Minimum cycle time	2.3 ms
SIO supported	True
M-Sequence Capability	PREOPERATE = TYPE_0 with 1 byte on-request data OPERATE = TYPE_0 with 1 byte on-request data ISDU supported
Block Parameter	True
Data Storage	True

4.2 Process input data

Name	Byte.Bit-offset	Bit Length	Subindex access supported	Data Type	Value	Description
Output State	0.0	1	False	Boolean	false/true	
					false	Output Off
					true	Output On
Low Temperature Warning	0.1	1	False	Boolean	false/true	
					false	Temperature Ok
					true	Temperature Limit Exceeded
High Temperature Warning	0.2	1	False	Boolean	false/true	
					false	Temperature Ok
					true	Temperature Limit Exceeded
Target Out Of Range Warning	0.3	1	False	Boolean	false/true	
					false	Target In Range
					true	Target Out Of Range
Analog signal	0.4	12	False	UInteger	0...4095	

4.3 Standard parameters

Name	Index (dec.)	Index (hex.)	Sub-index (dec.)	Sub-index (hex.)	Subindex access supported	Access	Byte. Bit-offset	Bit Length	Data Type	Value	Default	Description
Min Cycle Time	0	0x0	3	0x3	True	read	2.0	8	UInteger			
IO-Link Version ID	0	0x0	5	0x5	True	read	4.0	8	UInteger		17	
Vendor ID 1	0	0x0	8	0x8	True	read	7.0	8	UInteger			
Vendor ID 2	0	0x0	9	0x9	True	read	8.0	8	UInteger			
Device ID 1	0	0x0	10	0xA	True	read	9.0	8	UInteger			
Device ID 2	0	0x0	11	0xB	True	read	10.0	8	UInteger			
Device ID 3	0	0x0	12	0xC	True	read	11.0	8	UInteger			
Standard Command	2	0x2	0	0x0	True	write	0.0	8	UInteger	0...159		System command
										64		Window Mode Teach (Point 1)
										65		Single Point Teach
										66		Teach To Window Mode (Point 2)
										67		Two Point Teach 1
										68		Window Mode Teach (Point 2)
										70		Two Point Teach 2
										75		Start Of Range Teach
										76		End Of Range Teach
										77		One Point Teach (+/- 5 % Span)
										128		Device Reset
129		Application Reset										
130		Restore Factory Settings										
Parameter (write) Access Lock	12	0xC	1	0x1	False	read/write	0.0	1	Boolean	false/true		Device access locks
Data Storage Lock	12	0xC	2	0x2	False	read/write	0.1	1	Boolean	false/true		Device access locks

Name	Index (dec.)	Index (hex.)	Sub-index (dec.)	Sub-index (hex.)	Subindex access supported	Access	Byte. Bit-offset	Bit Length	Data Type	Value	Default	Description
Local Parameterization Lock	12	0xC	3	0x3	False	read/write	0.2	1	Boolean	false/true		Device access locks
Local User Interface Lock	12	0xC	4	0x4	False	read/write	0.3	1	Boolean	false/true		Device access locks
Vendor Name	16	0x10	0	0x0	True	read	0.0	32	String		Turck	Vendor name
Vendor Text	17	0x11	0	0x0	True	read	0.0	32	String		www.turck.com	Additional manufacturer information
Product Name	18	0x12	0	0x0	True	read	0.0	32	String			Manufacturer's device designation
Product ID	19	0x13	0	0x0	True	read	0.0	32	String			Ident-No.
Product Text	20	0x14	0	0x0	True	read	0.0	32	String			Device category
Serial Number	21	0x15	0	0x0	True	read	0.0	16	String			Device serial number
Hardware Version	22	0x16	0	0x0	True	read	0.0	32	String			Hardware revision
Firmware Version	23	0x17	0	0x0	True	read	0.0	16	String			Firmware revision
Application Specific Tag	24	0x18	0	0x0	True	read/write	0.0	32	String		***	Any user generated content
Process Data Input	40	0x28	0	0x0	True	read	0.0	0	Process-Data-InUnion			

4.4 Parameters

Name	Index (dec.)	Index (hex.)	Sub-index (dec.)	Sub-index (hex.)	Subindex access supported	Access	Byte. Bit Offset	Bit Length	Data Type	Value	Default	Description
Switch Point 1	60	0x3C	1	0x1	True	read/write	0.0	16	UInteger	0...4095	3800	
Switch Point 2	60	0x3C	2	0x2	True	read/write	2.0	16	UInteger	0...4095	520	
Inversion	61	0x3D	1	0x1	True	read/write	0.0	8	UInteger	0...1	0	
										0		Normally Open
										1		Normally Close
Operation Mode	61	0x3D	2	0x2	True	read/write	1.0	8	UInteger	1...128	1	
										1		Single Point Mode
										2		Window Mode
										3		Two Point Mode
										128		Temperature Alert
Hysteresis Value	61	0x3D	3	0x3	True	read/write	2.0	16	UInteger	50...100	100	
										50		Small
										100		Standard
PNP/NPN	61	0x3D	4	0x4	True	read/write	4.0	8	UInteger	0...1	0	
										0		PNP
										1		NPN
Start Of Range (0% Output)	64	0x40	1	0x1	True	read/write	0.0	16	UInteger	0...4095	0	
End Of Range (100% Output)	64	0x40	2	0x2	True	read/write	2.0	16	UInteger	0...4095	4095	
Output Voltage Range	64	0x40	3	0x3	True	read/write	4.0	8	UInteger	0...1	0	
										0		0...10 V
										1		2...10 V
Actual Temperature	65	0x41	1	0x1	True	read/write	0.0	8	Integer	-128...127	25	
Application Low Temp. Alert	65	0x41	2	0x2	True	read/write	1.0	8	Integer	-128...127	-25	
Application High Temp. Alert	65	0x41	3	0x3	True	read/write	2.0	8	Integer	-128...127	70	

Name	Index (dec.)	Index (hex.)	Sub-index (dec.)	Sub-index (hex.)	Subindex access supported	Access	Byte. Bit Offset	Bit Length	Data Type	Value	Default	Description
Temperature Unit	65	0x41	4	0x4	True	read/write	3.0	8	UInteger	0...2	0	
										0		°C
										1		°F
Lowest Temperature	74	0x4A	1	0x1	True	read	0.0	8	Integer	-128	-25	
										...	127	
Highest Temperature	74	0x4A	2	0x2	True	read	1.0	8	Integer	-128	70	
										...	127	
Damping (ms)	82	0x52	0	0x0	True	read/write	0.0	16	UInteger	0...4095	0	
teach state	258	0x102	0	0x0	True	read	0.0	8	UInteger	0...1	0	
										0		last teach invalid
										1		last teach OK

TURCK

Over 30 subsidiaries and over
60 representations worldwide!

100014074 | 2020/01



www.turck.com