






MALE END VIEW		FEMALE END VIEW	SPECIFICATIONS																									
			<table><tr><td>CONTACT CARRIER MATERIAL</td><td>TPU</td></tr><tr><td>MOLDED HEAD MATERIAL/COLOR</td><td>TPU/BLUE-GRAY</td></tr><tr><td>CONTACT MATERIAL/PLATING</td><td>BRASS/GOLD</td></tr><tr><td>COUPLING NUT MATERIAL/PLATING</td><td>BRASS/NICKEL</td></tr><tr><td>RATED CURRENT [A]</td><td>7.0 A</td></tr><tr><td>RATED VOLTAGE [V]</td><td>300 V</td></tr><tr><td>OUTER JACKET MATERIAL/COLOR</td><td>PVC/GREY</td></tr><tr><td>CONDUCTOR INSULATION MATERIAL</td><td>FOAMED HDPE (DATA), PVC (POWER)</td></tr><tr><td>NUMBER OF CONDUCTORS [AWG]</td><td>2x16 AWG, 2x20 AWG, 20 AWG DRAIN</td></tr><tr><td>SHIELD</td><td>FOIL (PAIRS), FOIL (OVERALL)</td></tr><tr><td>TEMPERATURE RATING</td><td>-40°C to +80°C (-40°F to +176°F)</td></tr><tr><td>PROTECTION CLASS</td><td>NEMA 1,3,4,6P,12 &amp; IECIP67, IP68,IP69,IP69K</td></tr></table>		CONTACT CARRIER MATERIAL	TPU	MOLDED HEAD MATERIAL/COLOR	TPU/BLUE-GRAY	CONTACT MATERIAL/PLATING	BRASS/GOLD	COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL	RATED CURRENT [A]	7.0 A	RATED VOLTAGE [V]	300 V	OUTER JACKET MATERIAL/COLOR	PVC/GREY	CONDUCTOR INSULATION MATERIAL	FOAMED HDPE (DATA), PVC (POWER)	NUMBER OF CONDUCTORS [AWG]	2x16 AWG, 2x20 AWG, 20 AWG DRAIN	SHIELD	FOIL (PAIRS), FOIL (OVERALL)	TEMPERATURE RATING	-40°C to +80°C (-40°F to +176°F)	PROTECTION CLASS	NEMA 1,3,4,6P,12 & IECIP67, IP68,IP69,IP69K
CONTACT CARRIER MATERIAL	TPU																											
MOLDED HEAD MATERIAL/COLOR	TPU/BLUE-GRAY																											
CONTACT MATERIAL/PLATING	BRASS/GOLD																											
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL																											
RATED CURRENT [A]	7.0 A																											
RATED VOLTAGE [V]	300 V																											
OUTER JACKET MATERIAL/COLOR	PVC/GREY																											
CONDUCTOR INSULATION MATERIAL	FOAMED HDPE (DATA), PVC (POWER)																											
NUMBER OF CONDUCTORS [AWG]	2x16 AWG, 2x20 AWG, 20 AWG DRAIN																											
SHIELD	FOIL (PAIRS), FOIL (OVERALL)																											
TEMPERATURE RATING	-40°C to +80°C (-40°F to +176°F)																											
PROTECTION CLASS	NEMA 1,3,4,6P,12 & IECIP67, IP68,IP69,IP69K																											
 <b>DeviceNet™</b>		 <b>DeviceNet™</b>																										




CABLE LENGTH	TOLERANCE*
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE*
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm
* UNLESS OTHERWISE SPECIFIED	

SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:  
1. "\*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

H	UPDATE MALE TO LONG PIN	KB	02/28/25	81013
REV	DESCRIPTION	BY	DATE	ECO NO.

RELATED DOCUMENTS  1.  2.  3.  4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		<div>TURCK</div> <div>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us</div>		
						
	MATERIAL	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DRFT      CBM	DATE   08/10/00	DESCRIPTION  WSM RKM 5711-*M	
	FINISH		APVD	SCALE    1=1.3		
CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT  MILLIMETER [ INCH ]		IDENTIFICATION NO.		REV  H
		DO NOT SCALE THIS DRAWING		FILE: 777005138		SHEET 1 OF 1