



MALE END VIEW		FEMALE END VIEW		SPECIFICATIONS																									
				<table><tr><td>CONTACT CARRIER MATERIAL</td><td>TPU</td></tr><tr><td>MOLDED HEAD MATERIAL/COLOR</td><td>TPU/BLUE-GRAY</td></tr><tr><td>CONTACT MATERIAL/PLATING</td><td>BRASS/GOLD</td></tr><tr><td>COUPLING NUT MATERIAL/PLATING</td><td>BRASS/NICKEL</td></tr><tr><td>RATED CURRENT [V]</td><td>7.0 A</td></tr><tr><td>RATED VOLTAGE [V]</td><td>300 V</td></tr><tr><td>OUTER JACKET MATERIAL/COLOR</td><td>TPU/GRAY</td></tr><tr><td>CONDUCTOR INSULATION MATERIAL</td><td>FOAMED HDPE (DATA), PVC (POWER)</td></tr><tr><td>NUMBER OF CONDUCTORS [AWG]</td><td>2x17 AWG, 2x20 AWG, 20 AWG DRAIN</td></tr><tr><td>SHIELDING</td><td>FOIL (PAIRS), ALUM/POLYESTER FOIL (OVERALL)</td></tr><tr><td>TEMPERATURE RATING</td><td>-40° to +80°C (-40°F to +176°)</td></tr><tr><td>PROTECTION CLASS</td><td>NEMA 1,3,4,6P,12 &amp; IECIP67, IP68,IP69,IP69K</td></tr></table>		CONTACT CARRIER MATERIAL	TPU	MOLDED HEAD MATERIAL/COLOR	TPU/BLUE-GRAY	CONTACT MATERIAL/PLATING	BRASS/GOLD	COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL	RATED CURRENT [V]	7.0 A	RATED VOLTAGE [V]	300 V	OUTER JACKET MATERIAL/COLOR	TPU/GRAY	CONDUCTOR INSULATION MATERIAL	FOAMED HDPE (DATA), PVC (POWER)	NUMBER OF CONDUCTORS [AWG]	2x17 AWG, 2x20 AWG, 20 AWG DRAIN	SHIELDING	FOIL (PAIRS), ALUM/POLYESTER FOIL (OVERALL)	TEMPERATURE RATING	-40° to +80°C (-40°F to +176°)	PROTECTION CLASS	NEMA 1,3,4,6P,12 & IECIP67, IP68,IP69,IP69K
CONTACT CARRIER MATERIAL	TPU																												
MOLDED HEAD MATERIAL/COLOR	TPU/BLUE-GRAY																												
CONTACT MATERIAL/PLATING	BRASS/GOLD																												
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL																												
RATED CURRENT [V]	7.0 A																												
RATED VOLTAGE [V]	300 V																												
OUTER JACKET MATERIAL/COLOR	TPU/GRAY																												
CONDUCTOR INSULATION MATERIAL	FOAMED HDPE (DATA), PVC (POWER)																												
NUMBER OF CONDUCTORS [AWG]	2x17 AWG, 2x20 AWG, 20 AWG DRAIN																												
SHIELDING	FOIL (PAIRS), ALUM/POLYESTER FOIL (OVERALL)																												
TEMPERATURE RATING	-40° to +80°C (-40°F to +176°)																												
PROTECTION CLASS	NEMA 1,3,4,6P,12 & IECIP67, IP68,IP69,IP69K																												
<p>1 = BARE (SHIELD) 2 = RED (+ VOLTAGE) 3 = BLACK (- VOLTAGE) 4 = WHITE (CAN_H) 5 = BLUE (CAN_L)</p>		<p>1 = BARE (SHIELD) 2 = RED (+ VOLTAGE) 3 = BLACK (- VOLTAGE) 4 = WHITE (CAN_H) 5 = BLUE (CAN_L)</p>																											
<b>DeviceNet™</b>		<b>DeviceNet™</b>																											



<div>NOTES:</div> <div>1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.</div>					RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		<div>TURCK</div> <div>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us</div>					
					1. 2. 3. 4.											
					MATERIAL		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY  CONTACT TURCK FOR MORE INFORMATION		DRFT RDS		DATE 05/07/02		DESCRIPTION  WSM WKM 5723-*M			
									APVD		SCALE 1=1.3					
					FINISH				UNIT OF MEASUREMENT  MILLIMETER [ INCH ]				IDENTIFICATION NO.			
I	UPDATE MALE TO LONG PIN			KB	02/28/25	81013		DO NOT SCALE THIS DRAWING				FILE: 777005146		SHEET 1 OF 1		
REV	DESCRIPTION			BY	DATE	ECO NO.										