


SPECIFICATIONS					
CONTACT CARRIER MATERIAL	NYLON or TPU				
MOLDED HEAD MATERIAL/COLOR	TPU/BLACK				
CONTACT MATERIAL/PLATING	BRASS/GOLD				
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL				
RATED CURRENT [A]	4.0 A				
RATED VOLTAGE [V]	250 V				
OUTER CABLE JACKET MATERIAL/COLOR	PVC/VIOLET				
CONDUCTOR INSULATION MATERIAL	POLYETHYLENE				
NUMBER OF CONDUCTORS [AWG]	2x22 AWG (SHIELDED DATA PAIR WITH 22 AWG DRAIN WIRE)				
SHIELDING	ALUM. MYLAR AND TINNED-COPPER BRAID				
TEMPERATURE RANGE	-30°C to +75°C (-22°F to +167°F)				
PROTECTION CLASS	MEETS IEC IP67				

SOURCE DRAWING - FOR REFERENCE ONLY



RELATED DOCUMENTS

02/15/1

DATE

34226

ECO NO.

CABLE LENGTH	TOLERANCE				
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER				
STRIP LENGTH	TOLERANCE				
0-7mm	±0.5mm				
8-29mm	±1.0mm				
30-49mm	±2.0mm				
50-69mm	±3.0mm				
70-100mm	±4.0mm				
OVER 100mm	±5.0mm				

NOTES:

REV DESCRIPTION

UPDATE PROTECTION CLASS

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

	RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	High Technology Sensors and Automation Controls		3000 CAMPUS MINNEAPOLIS, MI 1-800-544- (763) 553- (763) 553-0 turck.com	N 55441 7769 7300)708 fax
	MATERIAL		DRFT RDS	DATE 07/25/06	DESCRIPTION RKSW 45	55 *M	
		ALL DIMENSIONS DISPLAYED ON THIS	DSGN	SCALE 1=1.0	KNSW 4))—· v	
		DRAWING ARE FOR REFERENCE ONLY	UNIT OF ME	ASUREMENT			
ı	FINISH	KEI EKENGE ONEI			IDENTIFICATION NO.		REV
		CONTACT TURCK FOR MORE	MILLIMETE	ER[INCH]			l R
6		INFORMATION					
.]			DO NOT SCALE	THIS DRAWING	FILE: 777005679	SHEET	1 OF 1