


6 = GREEN (-RX) 7 = WHITE/BROWN 8 = BROWN

Ethernet

SPECII	FICATIONS
CONTACT CARRIER MATERIAL/COLOR (RJ45S)	POLYCARBONATE/CLEAR
MOLDED HEAD MATERIAL/COLOR (RJ45S)	TPU/BLACK
CONTACT MATERIAL/PLATING (RJ45S)	BRONZE/GOLD
RATED CURRENT [A]	1.5 A
RATED VOLTAGE [V]	42 V
OUTER CABLE JACKET MATERIAL/COLOR	TPE/TEAL
CONDUCTOR INSULATION MATERIAL	HDPE
NUMBER OF CONDUCTORS [AWG]	4UTPx24 AWG, STRANDED
SHIELDING	ALUMPOLYESTER FOIL, TINNED-COPPER BRAIDED
TEMPERATURE RANGE	-40° C to $+80^{\circ}$ C (-40° F to $+176^{\circ}$ F)
PROTECTION CLASS	IP20



CABLE LENGTH TOLERANCE * + 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH ALL LENGTHS WHICHEVER IS GREATER TOLERANCE* STRIP LENGTH 0-7mm ±0.5mm ±1.0mm 8-29mm 30-49mm ±2.0mm 50-69mm ±3.0mm 70-100mm ±4.0mm OVER 100mm ±5.0mm * UNLESS OTHERWISE SPECIFIED

SOURCE DRAWING - FOR REFERENCE ONLY

1. 2. 3. 4.
MATERIAL
FINISH

RELATED DOCUMENTS

FLEXLIFE:

APPROVALS:

ALL DIMENSIONS
DISPLAYED ON THIS
DRAWING ARE FOR
REFERENCE ONLY

CONTACT TURCK
FOR MORE
INFORMATION

POE COMPLIANT (802.3af): UP TO 80M LENGTH WHEN INSTALLED PER RECOMMENDATIONS IN TIA TSB-184

10X CABLE OD MIN: 1 MILLION CYCLES (TICK TOCK)

20X CABLE OD MIN: 10 MILLION CYCLES (TICK TOCK)

C(UL)US CMX-OUTDOOR-CM LISTED, AWM RECOGNIZED

COMPLIANT WITH NEC ARTICLE 800 COMMUNICATIONS CABLES

3RD ANGLE

PROJECTION

TORSION TEST: 3 MILLION CYCLES (11b LOAD, 360*-71 CYCLES/min)

THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.

RDS

APVD

High Technology Sensors and Automation Controls

MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com

3000 CAMPUS DRIVE

DATE 02/05/02 DESCRIPTION RJ45S 841-*M

UNIT OF MEASUREMENT IDENTIFICATION NO

UNIT OF MEASUREMENT

MILLIMETER [INCH]

DO NOT SCALE THIS DRAWING

FILE: 777005955

SHEET 1 OF 1

NOTES:

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

 N
 ADD CABLE SPECIFICATIONS
 KMY
 08/08/14
 46545

 EEV
 DESCRIPTION
 BY
 DATE
 ECO NO.