

## **Type Approval Certificate**

This is to certify that the undernoted product(s) has/have been tested with satisfactory results in accordance with the relevant requirements of the Lloyd's Register Type Approval System.

This certificate is issued to:

PRODUCER	Hans Turck GmbH & G Witzlebenstrasse, 7 45472 – Mülheim an de Germany		
PLACE OF PRODUCTION	Via Monte Fiorino, 9 37057 San Giovanni Lu Italy	ipatoto (VR)	
DESCRIPTION	HMIs (Human Machine Interfaces) with display and touchscreen, and plug-in accessories		
ТҮРЕ	eX700 Series: with the following plu	TX705-P3CV01 <sup>(*)</sup> TX707-P3CV01 <sup>(*)</sup> TX710-P3CV01 <sup>(*)</sup> g-in accessories: TX-CAN <sup>(*)</sup> TX-RS485 <sup>(*)</sup>	TX715-P3CV01 <sup>(*)</sup> TX721-P3CV01 <sup>(*)</sup> TX-IO-XX-03 <sup>(*)</sup> TX-IO-DX03 <sup>(*)</sup>
	<sup>(*)</sup> model name can be follow affecting LR Technical Requi	wed by 0 or 1 or 2 or 3 chara	cters identifying cosmetic parts not
APPLICATION	Marine, Offshore and Industrial application for use in environmental categories ENV1 and ENV2 as defined in Lloyd's Register's Type Approval System, Test Specification Number 1, 2017.		
SPECIFIED STANDARDS	Manufacturer's Specifi	ication	
Certificate No.	19/00008		
Issue Date	11 February 2019		M
Expiry Date	10 February 2024		auitio a

M. Crucil Trieste Technical Support Office Lloyd's Register EMEA

Lloyd's Register EMEA 71 Fenchurch Street, London EC3M 4BS

1 of 4

Sheet

Lloyd's Register EMEA Is a subsidiary of Lloyd's Register Group



## RATINGS

Power supply:	24 V dc	
Protection Index:	IP 66 (front)	
	IP 20 (rear)	
TX705-P3CV01		
- Display - Colours:	5″ TFT 16:9 LED – 64K	
- Resolution:	800x480 WVGA	
- Touchscreen:	True glass projected capacitive, multitouch	
- CPU:	ARM Cortex-A8 - 1GHz	
- Operating System:	Linux RT	
- Interfaces	n.2 Ethernet port	
	n.1 USB port	
	n.1 serial port (n.2 using plug-in modules)	
	SD card slot	
	n.1 plug-in module slot for system expansion	
TX707-P3CV01		
- Display - Colours:	7″ TFT 16:9 LED – 16M	
- Resolution:	800x480 WVGA	
- Touchscreen:	True glass projected capacitive, multitouch	
- CPU:	ARM Cortex-A9 dual core 800 MHz	
- Operating System:	Linux RT	
- Interfaces	n.3 Ethernet port	
	n.2 USB port	
	n.1 serial port (n.3 using plug-in modules)	
	SD card slot	
	n.2 plug-in module slots for system expansion	
TX710-P3CV01		
- Display - Colours:	10.1" TFT 16:9 LED - 16M	
- Resolution:	1280x800 WXGA	
- Touchscreen:	True glass projected capacitive, multitouch	
- CPU:	ARM Cortex-A9 dual core 800 MHz	
- Operating System:	Linux RT	
- Interfaces	n.3 Ethernet port	
	n.2 USB port	
	n.1 serial port (n.3 using plug-in modules)	
	SD card slot	
	n.2 plug-in module slots for system expansion	

Certificate No.

11 February 2019

**Expiry Date** 

Sheet

**Issue Date** 

10 February 2024

19/00008

2 of 4

Mausiñon

M. Crucil Trieste Technical Support Office Lloyd's Register EMEA

Lloyd's Register EMEA 71 Fenchurch Street, London EC3M 4BS

Lloyd's Register EMEA Is a subsidiary of Lloyd's Register Group



TX715-P3CV01		
- Display - Colours:	15.6" TFT LED – 16M	
- Resolution:	1366x768 HD	
- Touchscreen:	True glass projected capacitive, multitouch	
- CPU:	ARM Cortex-A9 quad core 800 MHz	
- Operating System:	Linux RT	
- Interfaces	n.3 Ethernet port	
	n.2 USB port	
	n.1 serial port (n.3 using plug-in modules)	
	SD card slot	
	n.2 plug-in module slots for system expansion	
TX721-P3CV01		
- Display - Colours:	21.5" TFT LED - 16M	
- Resolution:	1920x1080 HD	
- Touchscreen:	True glass projected capacitive, multitouch	
- CPU:	ARM Cortex-A9 quad core 800 MHz	
- Operating System:	Linux RT	
- Interfaces	n.3 Ethernet port	
	n.2 USB port	
	n.1 serial port (n.3 using plug-in modules)	
	SD card slot	
	n.2 plug-in module slots for system expansion	
Accessories:		
TX-CAN	CAN interface, DB9 CAN connector	
	CAN interface, DB9 CAN connector	

Accessories:			
TX-CAN	CAN interface, DB9 CAN connector		
TX-RS485	RS-422/485 interface with optical insulation		
TX-IO-XX03	I/O module		
	- 20 digital input		
	- 12 digital output		
	- 8 analogue input		
	- 1 Pt100 cold junction input		
	- 4 analogue output		
TX-IO-DX03	I/O module, compact		
	- 8 digital input		
	- 6 digital output		
	- 1 relay output		

Certificate No. 19/00008

Issue Date 11 February 2019

**Expiry Date** 

Sheet

10 February 2024

3 of 4

Maurino

M. Crucil Trieste Technical Support Office Lloyd's Register EMEA

Lloyd's Register EMEA 71 Fenchurch Street, London EC3M 4BS

Lloyd's Register EMEA Is a subsidiary of Lloyd's Register Group



## ADDITIONAL TESTS

Compass Safe Distance, according to IEC 60945:2002

	standard	steering	
	compass [m]	compass [m]	
TX705-P3CV01	0.15	0.10	
TX707-P3CV01	0.85	0.40	
TX710-P3CV01	1.15	0.75	
TX715-P3CV01	1.80	1.30	
TX721-P3CV01	2.20	1.30	

Cold test, IEC 60068-2-1, cl.6: at -25°C, 5 hours Dry Heat test, IEC 60068-2-2, cl.6: at +55°C, 16 hours

"This Certificate is not valid for equipment, the design, ratings or operating parameters of which have been varied from the specimen tested. The manufacturer should notify Lloyd's Register EMEA of any modification or changes to the equipment in order to obtain a valid certificate."

The Design Appraisal Document No.19/00008 and its supplementary Type Approval Terms and Conditions form part of this Certificate.



M. Crucil Trieste Technical Support Office Lloyd's Register EMEA

**Issue Date** 11 Fe

Certificate No.

19/00008

10 February 2024

11 February 2019

**Expiry Date** 

Sheet

4 of 4

Lloyd's Register EMEA 71 Fenchurch Street, London EC3M 4BS

> Lloyd's Register EMEA Is a subsidiary of Lloyd's Register Group