

Translation

TUV NORD

(1) **EU-Type Examination Certificate**

- (2) Equipment and protective systems intended for use in potentially explosive atmospheres, **Directive 2014/34/EU**



(3) **Certificate Number** TÜV 18 ATEX 195801 X **issue:** 00

(4) for the product: Solenoid driver type IMC-DO-11Ex/L

(5) of the manufacturer: Hans Turck GmbH & Co. KG

(6) Address: Witzlebenstraße 7
45472 Mülheim
Germany

Order number: 8000469449

Date of issue: 2018-11-14

- (7) The design of this product and any acceptable variation thereto are specified in the schedule to this EU-Type Examination Certificate and the documents therein referred to.
- (8) The TÜV NORD CERT GmbH, Notified Body No. 0044, in accordance with Article 17 of the Directive 2014/34/EU of the European Parliament and the Council of 26 February 2014, certifies that this product has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of products intended for use in potentially explosive atmospheres given in Annex II to the Directive.
The examination and test results are recorded in the confidential ATEX Assessment Report No. 18 203 195801.
- (9) Compliance with the Essential Health and Safety Requirements has been assured by compliance with:

EN 60079-0:2012 + A11:2013
EN 60079-31:2014

EN 60079-7:2015

EN 60079-11:2012

except in respect of those requirements listed at item 18 of the schedule.

- (10) If the sign "X" is placed after the certificate number, it indicates that the product is subject to the Specific Conditions for Use specified in the schedule to this certificate.
- (11) This EU-Type Examination Certificate relates only to the design, and construction of the specified product. Further requirements of the Directive apply to the manufacturing process and supply of this equipment. These are not covered by this certificate.
- (12) The marking of the product shall include the following:

II (1) G [Ex ia Ga] IIC/IIB
II (1) D [Ex ia Da] IIIC/IIIB
 II 3 (1) G Ex ec [ia Ga] IIC/IIB T4 Gc
II 3 (1) D Ex tc [ia Da] IIIB T86 °C Dc

TÜV NORD CERT GmbH, Langemarckstraße 20, 45141 Essen, notified by the central office of the countries for safety engineering (ZLS), Ident. Nr. 0044, legal successor of the TÜV NORD CERT GmbH & Co. KG Ident. Nr. 0032

The head of the notified body

Roder

Hanover office, Am TÜV 1, 30519 Hannover, Tel. +49 511 998-61455, Fax +49 511 998-61590

This certificate may only be reproduced without any change, schedule included.
Excerpts or changes shall be allowed by the TÜV NORD CERT GmbH

(13) SCHEDULE

(14) EU-Type Examination Certificate No. TÜV 18 ATEX 195801 X issue 00

(15) Description of product

The solenoid driver type IMC-DO-11Ex/L is used for the supply of passive two-poles (e. g. solenoid valves, signal lamps and two wire transmitters) as well as for the safe galvanic separation of the intrinsically safe circuit and the non-intrinsically safe circuit.

The intrinsically safe output circuit is safely galvanically separated from the non-intrinsically safe circuit up to the peak crest value of the voltage of 375 V.

Type code:

IMC-DO-11Ex/L

Electrical data:

Supply circuit

(Connections X2;

pins 1[+], 3[-] or 4[+], 3[-])

only for the connection to a non-intrinsically safe circuit with following maximum values:

$U_N = 24 \text{ V d.c (max. 30 V d.c), P ca. 3W}$

$U_m = 253 \text{ V a.c resp. 125 V d.c}$

Output circuit

(Connections X1;

bushings 1 [+], 3 [-])

in type of protection Intrinsic Safety Ex ia IIC/IIB/IIIC with following maximum value per circuit:

$U_o = 27 \text{ V}$

$I_o = 95 \text{ mA}$

$P_o = 674 \text{ mW}$

$R = 297 \Omega$

Characteristic line: trapezoidal

The effective internal capacitances and inductances are negligibly small.

The maximum permissible values for the external inductance L_o and the external capacitance C_o have to be taken from the following table:

Ex ia IIC	$L_o [\text{mH}]$	0.8	0.5	0.2	-	-
	$C_o [\mu\text{F}]$	0.058	0.07	0.09	-	-
Ex ia IIB / IIB / IIIC	$L_o [\text{mH}]$	13	2	0.5	0.2	0.1
	$C_o [\mu\text{F}]$	0.27	0.31	0.45	0.6	0.705

The maximum values of the table are also allowed to be used up to the permissible limits as concentrated capacitances and as concentrated inductances.

Thermal data:

Ambient temperature range:

$-25 \text{ }^\circ\text{C} \leq T_a \leq +70 \text{ }^\circ\text{C}$

(16) Drawings and documents are listed in the ATEX Assessment Report No. 18 203 195801.

Schedule to EU-Type Examination Certificate No. TÜV 18 ATEX 195801 X issue 00

(17) Specific Conditions for Use

1. For applications that require devices of EPL Gc and EPL Dc: The connecting and disconnecting of the energised non-energy limited circuit is not permitted when live.
2. For applications that require devices of EPL Gc and EPL Dc: The protective housing has to be safely screwed to a solid basement with the provided screws resp. with screws according to the manufacturer's manual.
3. For applications that require devices of EPL Dc: The value for the surface temperature was measured without dust layer.
4. For applications that require devices of EPL Dc: The dust is only allowed to be non-conductive.
5. For applications that require devices of EPL Dc: The solenoid driver type IMC-DO-11Ex/L has to be protected from electrostatic charging.

(18) Essential Health and Safety Requirements
No additional ones

- End of Certificate -