



IECEx Certificate of Conformity

INTERNATIONAL ELECTROTECHNICAL COMMISSION IEC Certification Scheme for Explosive Atmospheres

for rules and details of the IECEx Scheme visit www.iecex.com

Certificate No.: IECEx TUN 07.0009X Issue No.: 0 Certificate history:

Status: Current

Date of Issue: 2007-08-15 Page 1 of 5

Applicant: Hans Turck GmbH & Co. KG
Witzlebenstraße 7
D-45472 Mülheim an der Ruhr
Germany

Electrical Apparatus: Solenoid driver type IMC-DO-11Ex/L
Optional accessory:

Type of Protection: Intrinsic safety "i", type of protection "n" electrical apparatus, protection by enclosures "d"

Marking: [Ex ia] IIB/IIC
Ex nA [nL] IIB/IIC T4
Ex ID A22 IP67 T85°C

Approved for issue on behalf of the IECEx
Certification Body: Herbert Stürwald
Position: Head of ExCB

Signature:
(for printed version)

Date: 2007-8-15

1. This certificate and schedule may only be reproduced in full.
2. This certificate is not transferable and remains the property of the issuing body.
3. The Status and authenticity of this certificate may be verified by visiting the Official IECEx Website.

Certificate issued by:

TÜV NORD CERT GmbH
Hannover Office
Am TÜV 1
30519 Hannover
Germany



IECEx Certificate of Conformity

Certificate No.: IECEx TUN 07.0009X
Date of Issue: 2007-08-15 Issue No.: 0
Page 2 of 5

Manufacturer: Werner Turck GmbH & Co. KG
Goethestraße 7
D-58553 Halver
Germany

Manufacturing location(s):

This certificate is issued as verification that a sample(s), representative of production, was assessed and tested and found to comply with the IEC Standard 1st below and that the manufacture's quality system, relating to the Ex products covered by this certificate, was assessed and found to comply with the IECEx Quality system requirements. This certificate is granted subject to the conditions as set out in IECEx Scheme Rules, IECEx 02 and Operational Documents as amended.

STANDARDS:
The electrical apparatus and any acceptable variations to it specified in the schedule of this certificate and the identified documents, was found to comply with the following standards:

IEC 60079-0 : 2004 Edition: 4.0	Electrical apparatus for explosive gas atmospheres - Part 0: General requirements
IEC 60079-11 : 1999 Edition: 4	Electrical apparatus for explosive gas atmospheres - Part 11: Intrinsic safety "i"
IEC 60079-15 : 2005-03 Edition: Ed 3	Electrical apparatus for explosive gas atmospheres Part 15: Construction, test and Marking of Type of Protection "n" electrical apparatus
IEC 61241-0 : 2004 Edition: 1	Electrical apparatus for use in the presence of combustible dust - Part 0: General requirements
IEC 61241-1 : 2004 Edition: 1	Electrical apparatus for use in the presence of combustible dust - Part 1: Protection by enclosures "d"

This Certificate does not indicate compliance with electrical safety and performance requirements other than those expressly included in the Standards listed above.

TEST & ASSESSMENT REPORTS:
A sample(s) of the equipment listed has successfully met the examination and test requirements as recorded in

Test Report:
DE/TUNEXTR07.0011/00

Quality Assessment Report:
DE/PTBQAR06.0012/00



IECEx Certificate of Conformity

Certificate No.: IECEx TUN 07.0009X

Date of Issue: 2007-06-15

Issue No.: 0

Page 3 of 5

Schedule

EQUIPMENT:

Equipment and systems covered by this certificate are as follows:

The solenoid driver type IMC-DO-11Ex/L is an associated electrical apparatus for installation outside of the explosion hazardous area according to IEC 60 079-11 resp. an apparatus according to IEC 60 079-15 for use in zone 2 explosion hazardous areas.

It is also an apparatus according to IEC 61241-1 for use in zone 22 explosion hazardous areas.

It is used for the supply of passive two-poles (e. g. solenoid valves, signal lamps and two wire transmitters) as well as for the safe galvanic separation of the intrinsically safe resp. energy limited output circuit and the non intrinsically safe resp. non energy limited input circuit.

The marking as associated intrinsically safe apparatus outside the explosion hazardous area is

[Ex ia] IIC/IIB.

The marking for mounting in explosion hazardous areas of zone 2 is

Ex nA [nL] IIC/IIB T4.

The marking for mounting in explosion hazardous areas of zone 22 is

Ex tD A22 IP67 T86°C

The permissible ambient temperature range is -25°C ... 70°C.

CONDITIONS OF CERTIFICATION: YES as shown below:

1. For zone 2 and zone 22 applications: The connecting and disconnecting of energised non energy limited circuits is not permitted (see warning label).
2. Zone 2 and zone 22 applications: The protective housing has to be safely screwed to a solid basement with the provided screws resp. with screws according to the manufacturer's manual.
3. Zone 22 applications: The value for the surface temperature was measured without dust layer.
4. Zone 22 applications: The dust is only allowed to be non conductive.



IECEx Certificate of Conformity

Certificate No.: IECEx TUN 07.0009X

Date of Issue: 2007-06-15

Issue No.: 0

Page 4 of 5

EQUIPMENT(continued):

Electrical Data

Input circuit
(Connections X2;pins 1[+], 3[-]
or 4[+], 3[-])

$U = 24 \text{ V d. c. (max. 30 V d. c.)}$, $P \text{ ca. } 3 \text{ W}$
For applications of the solenoid driver with marking
[Ex ia] IIC/IIB:
 $U_m = 250 \text{ V a. c. resp. } 125 \text{ V d. c.}$

Output circuit
(Connections X1;bushings 1 [+],
3 [-])

Maximum values:
 $U_o = 27 \text{ V}$
 $I_o = 95 \text{ mA}$
 $P_o = 674 \text{ mW}$
 $R = 297 \Omega$
Characteristic line: trapezoidal
The effective internal capacitances and inductances are
negligibly small.



IECEx Certificate of Conformity

Certificate No.: IECEx TUN 07.0009X

Date of issue: 2007-08-15

Issue No.: 0

Page 5 of 5

Additional information:

For applications with marking [Ex ia] IIC/IIB:

Ex ia	IIC		IIB	
max. permissible external inductance	0.75 mH	0.5 mH	2 mH	0.5 mH
max. permissible external capacitance	60 nF	70 nF	310 nF	450 nF

For applications with marking Ex nA [nL] IIC/IIB T4:

Ex nL	IIC		IIB	
max. permissible external inductance	4 mH	0.5mH	20 mH	5 mH
max. permissible external capacitance	74 nF	130 nF	490 nF	630 nF

The maximum values of the tables are also allowed to be used up to the permissible limits as concentrated capacitances and as concentrated inductances.

The intrinsically safe resp. energy limited circuits are safely galvanically separated from the non intrinsically safe resp. non energy limited circuits up to the peak crest value of the voltage of 375 V.