## Discrete Output Devices with Intrinsically Safe Field Circuits


NON-HAZARDOUS LOCATION or Class I, Div. 2, Group A, B, C or D or Class I, Zone 2, Group IIC

Power

R

Add IMXK devices

HAZARDOUS (CLASSIFIED) LOCATION
Class I, Div. 1, Groups A, B, C, D; Class II, Div. 1, Groups E, F, G; Class III, Div. 1
or
Class I, Zone O, Group IIC, IIB, or IIA




Entity Parameters: Class I, Division 1; Class II, Division 1; Class III, Division 1 Class I, Zone 0, 1, or 2 Circuit Characteristic: Angular

Model 1	Terminals	V <sub>oc</sub> / U <sub>o</sub> (V)	I <sub>sc</sub> / I <sub>o</sub> (mA)	R (Ω)	P <sub>o</sub> (mW)			L。/L。(mH)	
						AB/IIC	CDEFG/ IIB,IIA	AB/IIC	CDEFG/ IIB,IIA
IMX12-D001-2U-2U/	5-6	27.26	68.4	67.72	576	0.057	0.31	0.94	2
	7-8	27.26	68.4	67.72	576	0.057	0.31	0.94	2
IMX12-D001-1U-1U/	7-8	27.26	68.4	67.72	576	0.057	0.31	0.94	2
IMXK12-D001-1U-1U/	3-4	27.26	68.4	67.72	576	0.057	0.31	0.94	2

 $P_0$  is calculated using the formula  $P = (U_Q * I_0)/4 = (33.67V * 68.4mA)/4 = 576mW$ 



Associated Apparatus, non-hazardous locations or Class I, Division 2, Groups A, B, C and D Hazardous Locations, Class I, Zone 2, AEx nA [ia] IIC X, providing intrinsically safe circuits for use in Hazardous Locations Cl I, Division 1, Groups A, B, C, and D; Class II, Division 1, Groups E, F, and G; Class III, Division 1, and Zone O Group IIC. Install per Turck control drawing IS-1.314. www.turck.com/fmcd -25°C < Ta < +70°C Um = 253V Temp Code T4



<u></u>

a = Connection CC (cage clamp), or blank (screw clamp terminals)

Drawing No.:

IS-1.314

3000 Campus Drive Plmouth, MN 55441

www.Turck.com
UL Listed

Title: Control Drawing for UL Listed

IMX(K)12-D001-.U-../.. Discrete Output Isolated Barriers with I/S (Entity) Field Circuits

 A Release
 BVL
 8/24/15

 Rev
 Description
 Drft Chk Date
 Scale: NONE

RVI

4/5/19

Sheet

of

## Notes:

- ∱ Selected intrinsically safe equipment must be third party approved with correct entity parameters meeting the relations shown in Table 1, or simple apparatus.
- 2. Multiple circuits extending from the same piece of Associated Apparatus equipment must be installed in separate cables or in one cable having suitable insulation. Refer to International Society of Automation Recommended Practice ISA RP12.6 for installing intrinsically safe equipment.
- 3. A simple apparatus is defined as an electrical component or combination of components of simple construction with well-defined electrical parameters that does not generate more than 1.5V, 100mA, and 25mW, or a passive component that does not dissipate more than 1.3W and is compatable with the intrinsic safety of the circuit in which it is used.
- 4. Capacitance and inductance of the field wiring from the intrinsically safe equipment to the barrier should be calculated and should be included in the system calculations as shown in Table 1. Cable capacitance (Cc) plus intrinsically safe equipment capacitance (Ci) must be less than the marked capacitance (Ca) shown on any barrier used. The same applies for inductance (Lc, Li and La, respectively). Where the cable capacitance and inductance per foot are not known, the following values shall be used: Cc = 60 pF/ft, Lc = 0.2 uH/ft.


Table 1								
I.S. Equipment	Т	Barrier		I.S. Equipment		Barrier		
V <sub>max</sub>	≥	Voc (or V	t )	Ui	≥	Uo		
I <sub>max</sub>	≥	l <sub>sc</sub> (or l	t )	l <sub>i</sub>	≥	10		
C <sub>i</sub> + C <sub>cable</sub>	≤	Co		Ci+ Cc	≤	Ca		
Li+ Lcable	≤	Lo		Li+ Lc	≤	La		
Pi	≥	Po						

- 5. The barriers must be installed in accordance with barrier manufacturer's control drawing and Article 504 of the National Electrical Code, ANSI/NFPA 70, for installation in the United States.
- 6 Control equipment must not use or generate more than 253V rms or dc.
- 7. WARNING: EXPLOSION HAZARD To prevent ignition of flammable or combustive atmospheres, do not connect or disconnect when energized.

  AVERTISSEMENT: RISQUE D'EXPLOSION Pour éviter l'inflammation d'atmospherès inflammables ou combustibles, ne pas brancher ni debrancher sous tension.
- 8. WARNING: EXPLOSION HAZARD Substitution of components may impair intrinsic safety.

  AVERTISSEMENT: RISQUE D'EXPLOSION La substitution de composants peut compromettre la sécurité intrinsèque
- Connections: IMX12—D0 01—.U—-R/... devices may be connected to "Power Bridge" connectors installed on 35 mm DIN rail or attached directly to the DIN rail.

  IMX12—D0 01—.U—.U—0/... and IMXK12—D001—1U—1U—0/... devices must be attached directly to the DIN rail.
- 10. The maximum terminal tightening torque is 0.5 Nm.
- 11. The barriers must be installed in a Pollution Degree 2 environment.
- 12. The barriers must be installed in a final enclosure rated IP54 or better.
- 13. The maximum installation altitude is 2000 meters.
- 14. Use conductors rated 75°C minimum.



В	Add IMXK devices	BVL	4/5/19	Drawing No.:	IS-1.314				
Rev	Description	Drft	Date	Scale: None		Sheet	2	of	2