2	Product or Protective Sy	Product or Protective System Intended for use in Potentially Explosive Atmospheres			
	UKSI 207	16:1107 (as amended) – Sc	hedule 3A, Part 1		
3	Type Examination Certificate No.:	TÜV 22 UKEX 7114	Issue: 00		
4	Product:	Gateway, type GDP-IS			
5 6	Manufacturer: Address:	Hans Turck GmbH & Co H Witzlebenstraße 7	(G		
		45472 Mülheim an der Ru	hr, Germany		
7	This product and any acceptable variation thereto is specified in the schedule to this certificate and the documents therein referred to.				
8	TUV Rheinland UK Ltd, Approved Body number 2571, in accordance with Regulation 42 of the Equipment and Protective Systems Intended for Use in Potentially Explosive Atmospheres Regulations 2016, UKSI 2016:1107 (as amended), certifies that this product has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of products intended for use in potentially explosive atmospheres given in Schedule 1 of the Regulations.				
	The examination and test results an	re recorded in the confidentia	al report 557 / UKEx 7114.00 / 22.		
9	Compliance with the Essential Hea	Ith and Safety Requirements	has been assured by compliance with:		
	EN IEC 60079-0:2018	EN 60079-11:2012	EN 60079-25:2010		
	Except in respect of those requirem	nents listed at section 18 of t	he schedule to this certificate.		
10	If the sign "X" is placed after the cert of use specified in the schedule to t		at the product is subject to specific conditions		
11	This TYPE EXAMINATION CERTIFICATE relates only to the design and construction of the specified product. Further requirements of the Regulations apply to the manufacturing process and supply of this product. These are not covered by this certificate.				
12	The marking of this product shall in	clude the following:			
	⟨ <sub>€</sub> ⟩ II 2 G Ex	t ib IIC T4 Gb			
	This certificate and its schedules may only be reproduced in its entirety and without change.				
	TUV Rheinland UK Ltd		Solihull, 2023-02-02		
	DiplIng. Klauspeter Graffi				
	This Type Examination Certific TUV Rheinland UK Ltd, 101	ate without signature shall not be valid. A 1 Stratford Road, Shirley, Solihull, B90 4f JKAS accredited certification body, No. 8	3N, Tel. +44 (0) 121 7969400		

UNITED KINGDOM CONFORMITY ASSESSMENT

**UK TYPE EXAMINATION CERTIFICATE** 



1

MS-0045113 Attachment A3



all

## 13 SCHEDULE TO UK TYPE EXAMINATION CERTIFICATE

## 14 CERTIFICATE NUMBER TÜV 22 UKEX 7114

#### **15 Description of Product**

Gateway, type GDP-IS...

#### **General product information**

The excom module Gateway, type GDP-IS... is used as an interface between the internal communication circuits of the excom system and external RS485-IS-bus systems (Profibus DP). In addition, it provides system-internal connections to a second gateway intended for redundant operation, address circuits and CAN-Bus connections.

The Gateway, type GDP-IS... is part of the excom Fieldbus System certified under TÜV 22 UKEX 7116 U. It may be installed and operated in the module racks with backplane of the remote I/O-Fieldbus System. In combination with the enclosure of the module the degree of protection IP20 is provided for.

The equipment is intended for application inside the hazardous gas area of up to zone 1.

#### **Technical Data**

I.) AC-supply circuit	type of protection Intrinsic Safety Ex ib IIC only for connection to the intrinsically safe circuit according to IECEx PTB 13.0040 U
	Maximum values:
	U = 20 V AC (Amplitude)
	f = 300 kHz 314 kHz
	P = 1 W (power consumption)
	C <sub>i</sub> negligibly low
	L <sub>i</sub> negligibly low
The intrinsically safe AC-supply circuit is sa other circuits up to a peak value of the nom	fely electrically isolated from ground and from a inal voltage of 60 V.

	-
II.) Signal circuit (CAN-Bus)	system-internal circuit without facilities for external connections
IIIa.) Adress coding, internal communication	system-internal circuit without facilities for external connections
IIIb.) Internal communication between GW1 and GW2	system-internal circuit without facilities for external connections
IV.) RS485-IS-Fieldbus terminal	type of protection Intrinsic Safety Ex ib IIC
(via D-SUB connector on system module rack, pins 3,5,6,8)	Maximum values: U₀ = 3.6 V I₀ = 125 mA

 $I_{\circ} = 125 \text{ mA}$   $P_{\circ} = 112.5 \text{ mW}$ linear characteristic  $U_i = 4.2 \text{ V}$ 



External RS485-IS-fieldbus terminaltype of protection Intrinsic Safety Ex ib IICMaximum values for each pair of terminals: $U_i = 4.2 V$ Maximum value, sum of all pairs of<br/>terminals: $I_i = 4.8 A$ Cables (loop resistance)type of cable A or B acc. to IEC 60079-25<br/>with the following parameters per unit<br/>length:L'/R'  $\leq 15 \mu H/\Omega$ <br/>C'  $\leq 250 nF/km$ <br/>strand wire diameter  $\geq 0.2 mm$ 

Concentrated reactances in the cable run of the external RS485-IS-fieldbus system are not permitted.

The intrinsically safe Profibus DP, RS485-IS, is safely electrically isolated from ground and from all other intrinsically safe circuits up to a peak value of the nominal voltage of 60 V.

The permissible range of the ambient temperature is -20 °C up to 70 °C.

List of used equipment and components

Dev	vice	Manufacturer	Туре	Ex-Marking	Certificate no.
non	e				

#### 16 Test report No. (associated with this certificate issue): 557 / UKEx 7114.00 / 22

# 17 Schedule of Limitations none

### 18 Essential Health and Safety Requirements (Regulations Schedule 1)

In addition to the Essential Health and Safety Requirements covered by the standards listed at item 9, all other requirements are demonstrated in the relevant reports.

#### 19 Drawings and Documents

Reg. no.	Document title:	Document no.:	Rev.:	Date:
1.	Approval documentation GDP- IS (148 p.)	Approval documentation GDP-IS signed.pdf	00	29.01.2023