


NI35-CP40-FZ3X2 电感式传感器




技术数据

型号	NI35-CP40-FZ3X2
货号	13403
常用数据	
额定开关距离	35 mm
安装条件	非齐平
安全工作距离	$\leq (0.81 \times S_n) \text{ mm}$
修正系数	37#钢 = 1; 铝 = 0.3; 不锈钢 = 0.7; 黄铜 = 0.4
重复精度	$\leq 2 \% \text{ 满量程}$
温度漂移	$\leq \pm 10 \%$
磁滞	3...15 %
电气数据	
工作电压 U_B	20...250 VAC
工作电压 U_B	10...300 VDC
交流额定工作电流	$\leq 400 \text{ mA}$
额定直流工作电流 I_B	$\leq 300 \text{ mA}$
频率	$\geq 50 \dots \leq 60 \text{ Hz}$
漏电流	$\leq 1.7 \text{ mA}$
隔离测试电压	1.5 kV
浪涌电流	$\leq 8 \text{ A} (\leq 10 \text{ ms}, \text{最大} 5 \text{ Hz})$
I_B 时的压降	$\leq 6 \text{ V}$
输出性能	2线, 可编程式连接, 2线
最小开关电流	$\geq 3 \text{ mA}$
开关频率	0.02 kHz
机械数据	
设计	方型, CP40
尺寸	114 x 40 x 40 mm

特点


- 方型外壳，厚度40 mm
- 感应面可调9个方向
- 塑料, PBT-GF30-V0
- 高亮度 LED 指示灯
- 可全方位观测工作电压及开关状态
- 2线20...250 VAC交流
- 2线10...300 VDC直流
- 可编程连接 (常闭或常开)
- 端子盒

接线图



功能原理

电感式传感器以非接触和无磨损的方式检测金属物体。以无磨损和非接触的方式检测金属物体。电感式传感器通过铁氧体线圈上构成的RLC线圈产生磁场。



技术数据

外壳材料	塑料, PBT-GF30-V0, 黑
感应面材料	塑料, PBT-GF30-V0, 黄
电气连接	端子室
夹紧能力	≤ 2.5 mm²
环境条件	
工作温度	-25...+70 °C
防震动性	55 Hz (1 mm)
防冲击性	30 g (11 ms)
防护等级	IP67
MTTF	2283 年 符合SN 29500 (Ed.99) 40 °C认证
工作电压指示	2路LED指示灯, 绿
开关状态指示	2路LED指示灯, 红色

安装说明


安装说明/描述

The diagram illustrates the installation of a sensor on a rail. The top part shows a side view of the rail with two yellow sensor cubes. Dimensions are labeled: D is the distance between the centers of the two sensors; W is the total width of the rail; S is the distance from the center of a sensor to the right edge of the rail; N is the height of the rail; and B is the width of the sensor. The bottom part shows a front view of the rail with one sensor cube. Dimension G is the distance from the center of the sensor to the left edge of the rail. Dashed lines indicate the original positions of the components.


距离D	$4.5 \times B$
距离W	$3 \times S_n$
距离S	$1.5 \times B$
距离G	$6 \times S_n$
距离N	$1 \times B$
B有效面积宽度	40 mm

附件

STRM M20X1.5 SCHWARZ	6965902
----------------------	---------



JS025/037	69429
-----------	-------



BSS-CP40**6901318**

用于40 x 40 mm矩形外壳的安装夹
具；材料：PP

