


BI15-CP40-VN4X2 电感式传感器




技术数据

型号	BI15-CP40-VN4X2
货号	15790
常用数据	
额定开关距离	15 mm
安装条件	齐平
安全工作距离	$\leq (0.81 \times S_n) \text{ mm}$
修正系数	37#钢 = 1; 铝 = 0.3; 不锈钢 = 0.7; 黄铜 = 0.4
重复精度	$\leq 2 \%$ 满量程
温度漂移	$\leq \pm 10 \%$
磁滞	3...15 %
电气数据	
工作电压 U_B	10...65 VDC
纹波电压 U_{ss}	$\leq 10 \% U_{Bmax}$
额定直流工作电流 I_o	$\leq 200 \text{ mA}$
空载电流	$\leq 15 \text{ mA}$
漏电流	$\leq 0.1 \text{ mA}$
隔离测试电压	0.5 kV
短路保护	是/循环
I_o 时的压降	$\leq 1.8 \text{ V}$
断线/反极性保护	是/是
输出性能	4线, 互补触点, NPN
开关频率	0.15 kHz
机械数据	
设计	方型, CP40
尺寸	114 x 40 x 40 mm
外壳材料	塑料, PBT-GF30-V0, 黑

特点

- 方型外壳，厚度40 mm
- 感应面可调9个方向
- 塑料, PBT-GF30-V0
- 高亮度 LED 指示灯
- 可全方位观测工作电压及开关状态
- 4线直流, 10...65 VDC
- 可转换触点,npn输出
- 接线盒

接线图



功能原理


电感式传感器以非接触和无磨损的方式检测金属物体。以无磨损和非接触的方式检测金属物体。电感式传感器通过铁氧体线圈上构成的RLC线圈产生磁场。

技术数据

感应面材料	塑料, PBT-GF30-V0, 黄
电气连接	端子室
夹紧能力	≤ 2.5 mm²
环境条件	
工作温度	-25...+70 °C
防震动性	55 Hz (1 mm)
防冲击性	30 g (11 ms)
防护等级	IP67
MTTF	2283 年 符合SN 29500 (Ed.99) 40 °C认证
工作电压指示	2路LED指示灯, 绿
开关状态指示	2路LED指示灯, 黄色

安装说明


安装说明/描述




The image contains two technical diagrams. The left diagram shows a side view of a sensor assembly mounted on a rail. It labels the total width of the assembly as 'W', the distance between the two sensor units as 'D', and the distance from the rail to the sensor units as 'S'. The right diagram shows a top-down view of the sensor units. It labels the width of a single sensor unit as 'B' and the distance between the centers of the two sensor units as 'G'.

距离D	2 x B
距离W	3 x Sn
距离S	1 x B
距离G	6 x Sn
B有效面积宽度	40 mm

附件

STRM M20X1.5 SCHWARZ	6965902
M20 × 1.5电缆防水接头	
	

JS025/037	69429
CK/CP40方型外壳的安装导轨；材质：VA 1.4301	
	

BSS-CP40	6901318
用于40 x 40 mm矩形外壳的安装夹具；材料：PP	
