


NI20-CP40-AP6X2 电感式传感器




技术数据

型号	NI20-CP40-AP6X2
货号	16024
常用数据	
额定开关距离	20 mm
安装条件	非齐平
安全工作距离	$\leq (0.81 \times S_n)$ mm
修正系数	37#钢 = 1; 铝 = 0.3; 不锈钢 = 0.7; 黄铜 = 0.4
重复精度	$\leq 2\%$ 满量程
温度漂移	$\leq \pm 10\%$
磁滞	3...15 %
电气数据	
工作电压 U_B	10...30 VDC
纹波电压 U_{ss}	$\leq 10\% U_{Bmax}$
额定直流工作电流 I_o	≤ 200 mA
空载电流	≤ 15 mA
漏电流	≤ 0.1 mA
隔离测试电压	0.5 kV
短路保护	是/循环
I_o 时的压降	≤ 1.8 V
断线/反极性保护	是/是
输出性能	3线, 常开触点, PNP
开关频率	0.15 kHz
机械数据	
设计	方型, CP40
尺寸	114 x 40 x 40 mm
外壳材料	塑料, PBT-GF30-V0, 黑

特点

- 方型外壳，厚度40 mm
- 感应面可调9个方向
- 塑料, PBT-GF30-V0
- 高亮度 LED 指示灯
- 可全方位观测工作电压及开关状态
- 3线直流, 10...30 VDC
- 常开, pnp输出
- 接线盒

接线图



功能原理

电感式传感器以非接触和无磨损的方式检测金属物体。以无磨损和非接触的方式检测金属物体。电感式传感器通过铁氧体线圈上构成的RLC线圈产生磁场。

技术数据

感应面材料	塑料, PBT-GF30-V0, 黄
电气连接	端子室
夹紧能力	≤ 2.5 mm²
环境条件	
工作温度	-25...+70 °C
防震动性	55 Hz (1 mm)
防冲击性	30 g (11 ms)
防护等级	IP67
MTTF	2283 年 符合SN 29500 (Ed.99) 40 °C认证
工作电压指示	2路LED指示灯, 绿
开关状态指示	2路LED指示灯, 黄色



安装说明

安装说明/描述

The image contains two technical drawings of a sensor assembly. The top drawing is a perspective view showing a yellow square sensor mounted on a grey rail. Dimension lines indicate: 'N' as the distance from the sensor face to the end of the rail, 'D' as the distance between two sensors, 'S' as the distance from a sensor to the end of the rail, and 'W' as the total length of the rail. The bottom drawing is a side view showing the sensor's profile. Dimension lines indicate: 'G' as the distance from the sensor face to the mounting bracket, and 'B' as the width of the sensor.

距离D	$3 \times B$
距离W	$3 \times S_n$
距离S	$1.5 \times B$
距离G	$6 \times S_n$
距离N	$0.5 \times B$
B有效面积宽度	40 mm

附件

STRM M20X1.5 SCHWARZ	6965902	JS025/037	69429
M20 × 1.5电缆防水接头		CK/CP40方型外壳的安装导轨；材质：VA 1.4301	
			

BSS-CP40**6901318**

用于40 x 40 mm矩形外壳的安装夹
具；材料：PP

