


NI10-K20-AZ3X 电感式传感器




技术数据

型号	NI10-K20-AZ3X
货号	43585
常用数据	
额定开关距离	10 mm
安装条件	非齐平
安全工作距离	$\leq (0.81 \times S_n) \text{ mm}$
修正系数	37#钢 = 1; 铝 = 0.3; 不锈钢 = 0.7; 黄铜 = 0.4
重复精度	$\leq 2 \%$ 满量程
温度漂移	$\leq \pm 10 \%$
磁滞	3...15 %
电气数据	
工作电压 U_B	20...250 VAC
工作电压 U_B	10...300 VDC
交流额定工作电流	$\leq 400 \text{ mA}$
额定直流工作电流 I_B	$\leq 300 \text{ mA}$
频率	$\geq 50 \dots \leq 60 \text{ Hz}$
漏电流	$\leq 1.7 \text{ mA}$
隔离测试电压	1.5 kV
浪涌电流	$\leq 8 \text{ A}$ ($\leq 10 \text{ ms}$, 最大5 Hz)
I_B 时的压降	$\leq 6 \text{ V}$
输出性能	2线, 常开触点, 2线
最小开关电流	$\geq 3 \text{ mA}$
开关频率	0.02 kHz
机械数据	
设计	光滑圆柱, 20 mm
尺寸	79 mm

特点


- 直径20mm 的光滑圆柱
- 塑料, PBT-GF30-V0
- 2线交流, 20...250 VAC
- 2线直流, 10...300 VDC
- 常开
- 电缆连接

接线图



功能原理

电感式传感器以非接触和无磨损的方式检测金属物体。以无磨损和非接触的方式检测金属物体。电感式传感器通过铁氧体线圈上构成的RLC线圈产生磁场。



技术数据

外壳材料	塑料, PBT-GF30-V0
感应面材料	塑料, PBT-GF30-V0
底帽	塑料, EPTR
电气连接	线缆
线缆材质	Ø 5.2 mm, LifYY, PVC, 2 m
导体横截面	2 x 0.34 mm²
环境条件	
工作温度	-25...+70 °C
防震动性	55 Hz (1 mm)
防冲击性	30 g (11 ms)
防护等级	IP67
MTTF	2283 年 符合SN 29500 (Ed.99) 40 °C认证
开关状态指示	LED指示灯, 红色
可供货	BS20

安装说明

安装说明/描述

The image contains three technical diagrams illustrating the installation of a BS20 sensor. The top diagram shows a side view of the sensor (a grey L-shaped bracket with two yellow pins) mounted on a wall. Dimensions are indicated: 'N' is the distance between the two pins, 'S' is the distance from the wall to the pins, 'D' is the distance from the wall to the sensor body, and 'W' is the distance from the wall to the sensor body. The bottom diagram shows a top-down view of the sensor mounted on a panel. Dimension 'T' is the distance from the wall to the sensor body. The bottom-right diagram shows a side view of the sensor mounted on a panel. Dimension 'G' is the distance from the wall to the sensor body.

距离D	$3 \times B$
距离W	$3 \times S_n$
距离T	$3 \times B$
距离S	$1.5 \times B$
距离G	$6 \times S_n$
距离N	$2 \times S_n$
B有效面积直径	$\varnothing 20 \text{ mm}$

附件

BS 20

69464

固定夹具，安装模块材质：PBT

