


BI2U-EG08-AP6X-H1341

电感式传感器 – 开关距离扩展




技术数据

型号	BI2U-EG08-AP6X-H1341
货号	4602034
常用数据	
额定开关距离	2 mm
安装条件	齐平
安全工作距离	$\leq (0.81 \times S_n) \text{ mm}$
重复精度	$\leq 2 \% \text{ 满量程}$
温度漂移	$\leq \pm 10 \%$
	$\leq \pm 20 \%, \leq -25^\circ\text{C} \vee \geq +70^\circ\text{C}$
磁滞	3...15 %
电气数据	
工作电压 U_B	10...30 VDC
纹波电压 U_{ss}	$\leq 10 \% U_{Bmax}$
额定直流工作电流 I_o	$\leq 150 \text{ mA}$
空载电流	$\leq 15 \text{ mA}$
漏电流	$\leq 0.1 \text{ mA}$
隔离测试电压	0.5 kV
短路保护	是/循环
I_o 时的压降	$\leq 1.8 \text{ V}$
断线/反极性保护	是/是
输出性能	3线, 常开触点, PNP
直流磁场稳定性	200 mT
交流电磁场稳定性	200 mT _{ss}
防护等级	IP68
开关频率	1 kHz
机械数据	
设计	螺纹, M8 x 1

特点

- M8 x 1圆柱螺纹
- 不锈钢1.4427SO
- 全金属检测衰减系数恒为1
- 防护等级IP68
- 抗磁场干扰
- 宽传感范围
- 高开关频率
- 非齐平安装
- 3线直流, 10...30 VDC
- 常开, pnp输出
- M12 x 1接插件

接线图



功能原理

电感式传感器采用无磨损和非接触的设计方式来检测金属物体。由于它特殊的多线圈的设计, 使得uprox+传感器拥有相当多的优势。它们拥有最佳的开关距离、最高的灵活性和操作可靠性以及高效的标准化, 尽显卓越不凡。

技术数据

尺寸	57 mm
外壳材料	不锈钢型, 1.4427 SO
感应面材料	塑料
外壳螺母的最大拧紧扭矩	5 Nm
电气连接	接插件, M12 × 1
环境条件	
工作温度	-30...+85 °C
防震动性	55 Hz (1 mm)
防冲击性	30 g (11 ms)
防护等级	IP68
MTTF	874 年 符合SN 29500 (Ed.99) 40 °C认证
开关状态指示	LED指示灯, 黄色

安装说明

安装说明/描述





The image contains four technical diagrams illustrating different installation methods for a sensor. 1. Top left: A side view of a square sensor with a central hole and a threaded rod passing through it. Dimension 'T' indicates the thickness of the sensor body. 2. Top right: A cross-sectional view of a T-shaped sensor. Dimension 'D' indicates the diameter of the threaded section. 3. Middle: Two views showing a sensor being inserted into a rectangular block. Dimension 'G' indicates the distance from the sensor's center to the edge of the block. 4. Bottom: A detailed cross-section of a sensor installed in a hole. The sensor has two threaded rods. Dimensions 'W', 'S', and 'D' are shown. 'W' is the width of the block, 'S' is the distance between the two rods, and 'D' is the diameter of the hole.

A cross-sectional view of a T-shaped sensor. The top part is a flat rectangular plate, and the bottom part is a threaded rod. Dimension 'D' is indicated as the diameter of the threaded section.

距离D	16 mm
距离W	6 mm
距离T	24 mm
距离S	12 mm
距离G	12 mm
B有效面积直径	Ø 8 mm

所有齐平式可安装型uprox+螺纹圆柱形均允许沉入式安装。此类传感器允许沉入半个螺纹安装，以保证使用安全。

附件

QM-08	6945100	快速安装支架单端封闭，M12 x 1公头镀铬黄铜接插件。注意：由于使用了快插支架，传感器的检测距离会衰减。	BST-08B	6947210	用于圆柱螺纹传感器的带塞子的安装夹具；材料：PA6
					
MW08	6945008	用于圆柱螺纹传感器的安装托架；材料：不锈钢 A2 1.4301 (AISI 304)	BSS-08	6901322	用于平滑圆柱型和圆柱螺纹传感器的安装夹具；材料：PP
					
MBS80	69479	用于平滑圆柱型传感器的安装夹具；安装块材料：电镀铝			
					

附件

尺寸图	型号	货号	
	RKH4-2/TFE	6935482	连接线缆，M12母头接插件（直式，3针），不锈钢联接螺母，线缆长度2 m，护套材质PVC，灰色；适用温度范围：-25...+80 °C
	RKH4-2/TFG	6934384	连接线缆，M12母头接插件（直式，3针），不锈钢联接螺母，线缆长度2 m，护套材质TPE，灰色；适用温度范围-40...+105 °C