



piconet rozšiřovací moduly pro IP-Link jednokanálový SSI interface SNNE-10S-0005




- SSI interface
- 1kanálový
- parametrizovatelné funkce
- nastavení pomocí I/O-ASSISTANT 2
- přímé připojení IP-Link
- pouzdro vyztužené skleněnými vlákny
- zalitá elektronika
- kovové konektory
- stupeň krytí IP67

enkodér - M23 x 1



Napájení M8 x 1



Typ	SNNE-10S-0005
ID č.	6824214
Napětí provozní/při zatížení	20...29 VDC
Provozní proud	≤ 55 mA
Délka LWL	≤ 15 m
Přenos bitů	diferenční (RS485)
Přenosová rychlost	až 1 MHz (standardně 250 Hz)
Sériový vstup	24 Bit
Směr toku dat	čtení
Napájení senzoru	24 VDC z napájení zátěže
Potenciálové oddělení	napájecí napětí RS232
Rozměry	30 x 126 x 26.5 mm
Odolnost vůči vibracím	dle EN 60068-2-6
Odolnost vůči rázům	dle EN 60068-2-27
Elektromagnetická kompatibilita (EMC)	dle EN 61000-6-2/EN 61000-6-4
Stupeň krytí	IP67
Certifikáty	CE, cULus

Procesní data

Pre-conditions	Address	Input data		Output data	
Compact mapping: Starting with D3 in "Low-Byte" word 0 all other bytes follow immediately (highlighted in grey). Complex mapping: Data are mapped with control and status byte	Word	High-Byte	Low-Byte	High-Byte	Low-Byte
	0	D3	SB	Reg1	CB
	1	D1	D2	reserved	Reg0
	2	reserved	D0	reserved	reserved