


FM-IM-2UPLI63FX

Flow Monitoring – For the Connection of FP Product Series Flow Sensors

IO-Link Device with Current and Transistor Outputs





Туре	FM-IM-2UPLI63FX
ID	100000819
Electrical data	
Operating voltage	2030 VDC
Power consumption	< 4.5 W
No-load current I₀	≤ 63 mA
Teach modes	Min/max adjustment. Teach modes incl. DeltaFlow monitoring (teach modes are automatically released with the change of flow speed).
Flow speed	[%] after min/max adjustment (permanent)
Medium temperature	[°C] with the SET button temporarily pressed
Repeatability flow rate	typical ± 1 % (of full scale)
Repeatability media temperature	typical ± 1 K
Measuring accuracy media temperature	typical ± 7 K
Switchpoint hysteresis media temperature	2 K
Input function	Connection of flow sensors (non-Ex sensors of the FP100/FP150 product series only!)
Sensor voltage	≤ 15 VDC
Sensor current	≤ 35 mA
Sensor current limitation	approx. 110 mA
Measuring frequency	5 Hz (every 200 ms with software filter)



Features

- ■Analog output for flow
- Transistor switching outputs for temperature and faults
- Teaching upper and lower flow limit
- ■LED band for indication of flow rate and media temperature
- Monitoring of operating and display range
- Detection of wire-break and short-circuit on the sensor side
- Standard IO or IO-Link operating mode
- Parametrized via pushbutton or software-supported via IO-Link

Functional principle

With the external processing unit type FM-IM-...FX, all non-Ex flow sensors of the FP100 series (immersion sensors) can be operated.

The flow module features four status LEDs as well as a 10-segment LED band for local monitoring. Software-based diagnostic options are also available to the user, such as wire-break and short-circuit on the sensor side. Furthermore, monitoring of flow rates and media temperatures within a predefined operating and display range.

The upper and lower limit are determined in relation to the analog output signal and taught in using the implemented teach mode. Working on the calorimetric principle, the connectible sensors not only detect the flow rate but also the media temperature.

The flow module can be operated either in IO-Link (IOL) or in standard IO (SIO) mode via the integrated IO-Link interface. In SIO mode, the switching outputs are operated in the standard way. In IOL mode the current process signal is transmitted cyclically as a 10 bit-serial value.



Technical data

Output functions							
Flow monitoring	Analog output						
Temperature monitoring	transistor output						
Error monitoring	transistor output						
Current range	420 mA / 204 mA parametrizable						
Load	< 600 Ω						
Characteristic	Output of probe signal, no linearization						
Error recognition	NAMUR error limits						
Switching characteristic	PNP						
Switching state	active high / active low parametrizable (transistor output error monitoring only active low)						
Switching voltage	2030 VDC						
Switching current	100 mA						
Electrical connections	5-pole removable reverse polarity protect ed terminal blocks						
Connection mode	screw connection						
Terminal cross-section	≥ 1.5≤ 2.5 mm²						
IO-Link							
IO-Link specification	V 1.1						
Transmission rate	38.4 kBit/s (COM 2)						
Transmission physics	Transmission physics 3-wire physics (PHY 2)						
Communication channel	Clamp 12 and via front panel jack COM (PC)						
Communication modes	Tool based engineering via FDT / DTM, IODD. Acyclic communication via On-Re quest Data Objects						
Included in the SIDI GSDML	Yes						
Tests/approvals							
Approvals	CE, C-UL U.S. submitted						
Electromagnetic compatibility (EMC)	Acc. to NE21						
Relative humidity	EN 60068-2-38						
Mechanical data							
Design	Signal processor						
Dimensions	89 x 110 x 27 mm						
Housing material	Polycarbonate/ABS						
Ambient temperature	-25+70 °C						
Mounting type	DIN rail mounting and mounting panel						
Protection class	IP20						
MTBF	117 Years						

Parametrization is initiated either via pushbutton or software-supported via IO-Link interface. The actual parametrization is then implemented via the tool-based DTM or IODD within the FDT frame PACTware™ or acyclically near the control via On-Request Data Objects (ORDO).



LED display


LED	Color	Status	Description					
Pwr	green	on	Operating voltage applied					
			Device ready for operation					
		flashing	Operating voltage applied					
			IO-Link communication active					
			(inverted flash with T on 900 ms and T off 100 ms)					
Flow	yellow	on	Active current output					
		flashing	Teach mode / display of diagnostic data					
			for specification see manual					
Temp	yellow	off	Switching output media temperature [low]					
		on	Switching output media temperature [high]					
		flashing	Teach mode / display of diagnostic data					
			for specification see manual					
Fault	Red	Off	Switching output fault [high]					
		On	Switching output flow [low]					
			(for error pattern in combination with LEDs see manual)					

For detailed description of the display patterns and flashing codes see instruction manual FM-IM/FMX-IM

IO-Link (Process Data Objects)

Bit	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	Flow Value 10 Bit (Bit 15 = MSB, Bit 6 = LSB)								not a	assigr	ned	Out 3	Out 2	Out1		
														(Fault)	(Temp)	(Flow)

Accessories



Accessories

