

PS510-600-03-LI2UPN8-H1141  
Pressure Sensor – Relative Pressure: 0...600 Bar



Technical data

|                                           |                                      |
|-------------------------------------------|--------------------------------------|
| Type                                      | PS510-600-03-LI2UPN8-H1141           |
| ID                                        | 100001601                            |
| Medium temperature                        | -40...+80 °C                         |
| Application area                          | Liquids and gases                    |
| Pressure range                            |                                      |
| Pressure type                             | Relative pressure                    |
| Pressure range                            | 0...600 bar                          |
|                                           | 0...8702.26 psi                      |
|                                           | 0...60 MPa                           |
| Admissible overpressure                   | ≤ 2400 bar                           |
| Burst pressure                            | ≥ 4000 bar                           |
| Response time                             | Typically 1 ms (max. 2.5 ms)         |
| Long-term stability                       | ± 0.2 % FS, /annum                   |
| Accuracy                                  | 0.25 % FS (LHR) at +25 °C using BFSL |
| Electrical data                           |                                      |
| Operating voltage U <sub>B</sub>          | 18...33 VDC                          |
| Short-circuit/reverse polarity protection | yes, cyclic / yes (voltage supply)   |
| Capacitive load                           | 100 nF                               |
| Insulation class                          | III                                  |
| Outputs                                   |                                      |
| Output 1                                  | Switching output or IO-Link mode     |
| Output 2                                  | Analog or switching output           |
| Switching output                          |                                      |
| Communication protocol                    | IO-Link                              |
| Output function                           | NO/NC, PNP/NPN                       |
| Rated operational current                 | 0.25 A                               |
| Switching frequency                       | ≤ 300 Hz                             |



Features

- 4-digit, 2-color (red/green), 12-segment display, rotatable by 180°
- Housing is rotatable after mounting the process connection
- Metal measuring cell
- Pressure range 0...600 bar relative
- 18...33 VDC
- NO/NC contact, PNP/NPN output, analog output (current/voltage), IO-Link SSP4.1.1
- Process connection 1/4" NPT male thread
- Connector device, M12 × 1

Wiring diagram



Functional principle

The pressure sensors from the P510 product series operate with fully welded metal measuring cells. As a result of the pressure acting on the metal substrate, a signal that is proportional to the pressure is generated and processed electronically. Depending on the sensor variant, the processed signal is available either as a switching or an analog output with an accuracy of 0.25 % of full scale. The rotatable sensor body and a variety

of process connections guarantee flexible process integration.

## Technical data

|                                                |                                                                                                                                                        |
|------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Switching point distance                       | ≥ 0.5 %                                                                                                                                                |
| Switch point:                                  | (Min. + 0.005 × range)...100 % of full scale                                                                                                           |
| Release point(s)                               | min. up to (SP - 0.005 × range)                                                                                                                        |
| Switching cycles                               | ≥ 100 mil.                                                                                                                                             |
| <b>Analog output</b>                           |                                                                                                                                                        |
| Current output                                 | 4...20 mA                                                                                                                                              |
| High level signal current                      | 20.5 mA                                                                                                                                                |
| Low level signal current                       | 3.8 mA                                                                                                                                                 |
| Load resistance current output                 | ≤ 0.5 kΩ                                                                                                                                               |
| Voltage output                                 | 0...10 V                                                                                                                                               |
| Load resistance voltage output                 | ≥ 8 kΩ                                                                                                                                                 |
| <b>IO-Link</b>                                 |                                                                                                                                                        |
| IO-Link specification                          | V 1.1                                                                                                                                                  |
| IO-Link port type                              | Class A                                                                                                                                                |
| Transmission physics                           | corresponds to 3-wire physics (PHY2)                                                                                                                   |
| Transmission rate                              | COM 2/38.4 kbps                                                                                                                                        |
| Process data width                             | 32 bit (of which 5 bits are not used)                                                                                                                  |
| Measured value information                     | 24 bit (16-bit process value + 8-bit scale)                                                                                                            |
| Switching point information                    | 3 bit                                                                                                                                                  |
| Frame type                                     | 2.2                                                                                                                                                    |
| Minimum cycle time                             | 6 ms                                                                                                                                                   |
| Function pin 4                                 | IO-Link                                                                                                                                                |
| Function Pin 2                                 | DI                                                                                                                                                     |
| Maximum cable length                           | 20 m                                                                                                                                                   |
| Programming                                    | FDT/DTM                                                                                                                                                |
| Profile support                                | Smart Sensor Profile (SSP4.1.1)                                                                                                                        |
| Included in the SIDI GSDML                     | In preparation                                                                                                                                         |
| <b>Programming</b>                             |                                                                                                                                                        |
| Programming options                            | start/end value analog output; switch/release points; PNP/NPN; NO/NC contact; hysteresis/window function; damping; pressure unit; peak pressure memory |
| <b>Mechanical data</b>                         |                                                                                                                                                        |
| Housing material                               | Stainless-steel/Plastic, 1.4404 (AISI 316L)/Grilamid TR90 UV/Elastollan C 65 A 15 HPM 000/Ultramid A3X2G5                                              |
| Materials (contact with media)                 | Stainless steel 1.4404 (AISI 316L)/1.4542 (AISI 630)                                                                                                   |
| Process connection                             | 1/4" NPT-18 male thread                                                                                                                                |
| Wrench size pressure connection / coupling nut | 24                                                                                                                                                     |
| Max. tightening torque of housing nut          | 35 Nm                                                                                                                                                  |
| Electrical connection                          | Connector, M12 × 1                                                                                                                                     |

## Technical data

|                                                 |                                                                                                                                                                                      |
|-------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Protection class                                | IP66<br>IP67<br>IP69K                                                                                                                                                                |
| <b>Environmental conditions</b>                 |                                                                                                                                                                                      |
| Ambient temperature                             | -40...+80 °C                                                                                                                                                                         |
| Storage temperature                             | -40...+80 °C                                                                                                                                                                         |
| Shock resistance                                | 50 g (11 ms) DIN EN 60068-2-27                                                                                                                                                       |
| EMV                                             | EN 61000-4-2 ESD:4 kV CD / 8 kV AD<br>EN 61000-4-3 HF radiated: 15 V/m<br>EN 61000-4-4 Burst: 2 kV<br>EN 61000-4-6 HF cable bound: 10 V<br>EN 61000-6-2 0.5 kV, 42 Ω<br>EN 61326-2-3 |
| <b>Tests/approvals</b>                          |                                                                                                                                                                                      |
| Approvals                                       | CE<br>Metrological certification (RUS)<br>cULus                                                                                                                                      |
| UL registration number                          | E183243                                                                                                                                                                              |
| <b>Reference conditions acc. to IEC 61298-1</b> |                                                                                                                                                                                      |
| Temperature                                     | -40...+85 °C                                                                                                                                                                         |
| Atmospheric pressure                            | 689...1300 hPa abs.                                                                                                                                                                  |
| Humidity                                        | 10...95 % rel.                                                                                                                                                                       |
| Auxiliary power                                 | 24 VDC                                                                                                                                                                               |
| <b>Displays/Operating elements</b>              |                                                                                                                                                                                      |
| Display                                         | 4-digit 12-segment display, rotatable by 180°, red or green                                                                                                                          |
| Switching state                                 | 2 × LEDs, Yellow                                                                                                                                                                     |
| Unit display                                    | 5 x LEDs green (bar, psi, kPa, MPa, misc)                                                                                                                                            |
| <b>Temperature behaviour</b>                    |                                                                                                                                                                                      |
| Temperature coefficient range $TK_s$            | ± 0.11 % of full scale/10 K                                                                                                                                                          |
| Temperature coefficient zero point $TK_0$       | ± 0.11 % of full scale/10 K                                                                                                                                                          |
| MTTF                                            | 100 years acc. to SN 29500 (Ed. 99) 40 °C                                                                                                                                            |



| Dimension drawing | Type   | ID        |                                                                  |
|-------------------|--------|-----------|------------------------------------------------------------------|
|                   | PAM-P3 | 100004416 | Damping element, protects the measuring cell from pressure peaks |

