


I/O Hub for Connection of Digital Signals to IO-Link Master

Eight Universal Digital Channels, PNP

FIL20-8DXP



Type	FIL20-8DXP
ID	100005646

Supply	
Supply voltage	24 VDC
Admissible range	18...30 VDC
	V1+ max. 8.7 A
System power supply	V1+
Voltage supply connection	Screw terminals
Operating current	120 mA
Sensor/actuator supply	VAUX supply from V1+
	Short-circuit proof, 0.7 A

System data	
Fieldbus connection technology	Screw terminals
Terminal cross-section	0.2...1.5 mm ² (AWG: 26...14)
Tightening torque	0.5 Nm

Digital inputs	
Number of channels	8
Connectivity inputs	Screw terminals
Type of input diagnostics	Channel diagnostics
Low-level signal voltage	-3...5 VDC (EN 61131-2, type 1 and 3)
High level signal voltage	11...30 VDC (EN 61131-2, type 1 and 3)
Max. input current	120 mA



Digital outputs	
Number of channels	8
Connectivity outputs	Screw terminals
Output type	PNP
Type of output diagnostics	Channel diagnostics
Output current per channel	1.0 A
Load type	Resistive, inductive, lamp load
Short-circuit protection	yes
Electrical isolation	500 VDC

- Rugged, I/O hub in IP20
- Eight universal digital channels
- Metal screw terminal connectors
- 8 universal digital channels, DI/DO
- 24 VDC, PNP
- Output current: 1.0 A
- I&M data sets support installation and maintenance
- IO-Link diagnostics for short-circuit and supply voltage

IO-Link	
Connectivity IO-Link	Screw terminals
IO-Link specification	V 1.1
IO-Link port type	Class A
Frame type	Supports all
Transmission rate	COM 2/38.4 kbps
Programming	FDT/DTM

Standard/Directive conformity	
Approvals and certificates	CE, UL

General Information	
Dimensions (W x L x H)	55 x 62.48 x 23.4 mm
Ambient temperature	-40...+70 °C
Storage temperature	-40...+85 °C
Altitude	Max. 5000 m
Protection class	IP20
MTTF	651 years acc. to SN 29500 (Ed. 99) 20 °C
Housing material	PA6-GF30
Housing color	Black
Mounting	Two mounting holes Ø 5 mm

		IO-Link Screw Terminals 1 = V1 + 2 = n.c. 3 = V1 - 4 = C/Q 5 = n.c. 
		I/O Screw Terminals 1 = V1 - 6 = I/O₄ 2 = I/O₀ 7 = I/O₅ 3 = I/O₁ 8 = I/O₆ 4 = I/O₂ 9 = I/O₇ 5 = I/O₃ 10 = V_{AUX} + 

Module LED status

LED indication	Color	Status	Description
IO-Link	Green	OFF	Power off
		Flashing	IO-Link communication OK, valid process data is being sent or received
	Red	ON	IO-Link communication or module error
		Flashing	IO-Link communication OK, invalid process data or diagnosis

Accessories

Type code	Ident no.		Dimension drawing
FDN20-BKT-DIN	Z0076	Mounting adapter for mounting of 8-channel Fxx20 modules on DIN rail (TS 35)	