



REI-E-113T8C-2B512-H1181

Incremental Encoder

Efficiency Line



Technical data

Type	REI-E-113T8C-2B512-H1181
ID	100011538
Measuring principle	Optical
General data	
Max. rotational speed	4500 rpm
Moment of inertia of the rotor	$1.8 \times 10^{-5} \text{ kgm}^2$
Starting torque	< 0.05 Nm
Output type	Incremental
Resolution incremental	512 ppr
Electrical data	
Operating voltage U_B	10...30 VDC
No-load current	$\leq 100 \text{ mA}$
Output current	$\leq 30 \text{ mA}$
Short-circuit protection	yes
Wire break/reverse polarity protection	yes
Pulse frequency max.	300 kHz
Signal level high	min. $U_B - 1 \text{ V}$
Signal level low	max. 0.5 V
Output function	Push-Pull/HTL, invertable
Mechanical data	
Flange type	Clamping flange
Flange diameter	$\varnothing 58 \text{ mm}$
Shaft Type	Solid shaft
Shaft diameter D (mm)	8
Shaft Length L [mm]	15
Shaft material	Stainless steel

Features

- Clamping flange, $\varnothing 58 \text{ mm}$
- Solid shaft, $\varnothing 8 \text{ mm} \times 15 \text{ mm}$
- Optical measuring principle
- Shaft material: stainless steel
- Protection class IP64 on housing and shaft side
- $-20 \dots +70 \text{ }^\circ\text{C}$
- Max. 4500 rpm (continuous operation 3000 rpm)
- 10...30 VDC
- Push-pull/HTL invertible
- Pulse frequency max. 300 kHz
- M12 $\times$ 1 male connector, 8-pin
- 512 pulses per revolution

Wiring diagram




Technical data

Housing material	Die-cast zinc
Electrical connection	Connector, M12 × 1
	8-pin
Axial shaft load	40 N
Radial shaft load	80 N
Environmental conditions	
Ambient temperature	-20...+70 °C
Vibration resistance (EN 60068-2-6)	100 m/s², 10...2000 Hz
Shock resistance (EN 60068-2-27)	1000 m/s², 6 ms
Protection class	IP64
Protection class shaft	IP64

Accessories


RCS-15-08-06 1545361

Bellows coupling, outer diameter:
15 mm, bore diameter: 8 mm/6 mm




RA-BC-20-06-08 100048778

Bellows coupling with aluminum hub
Ø 20 mm; d1 = 6 mm, d2 = 8 mm




RA-BC-20-08-08 100048780

Bellows coupling with aluminum hub
Ø 20 mm; d1 = 8 mm, d2 = 8 mm




RA-BC-20-08-10 100048781

Bellows coupling with aluminum hub
Ø 20 mm; d1 = 8 mm, d2 = 10 mm



RA-BC-20-08-12 100049106

Bellows coupling with aluminum hub
Ø 20 mm; d1 = 8 mm, d2 = 12 mm




Accessories

Dimension drawing	Type	ID	
	RKC8T-2/TXL	6625142	



Connection cable, M12 female
connector, straight, 8-pin, cable length:
2 m, jacket material: PUR, black; cULus
approval

Dimension drawing	Type	ID	
	WKC8T-2/TXL	6625145	Connection cable, M12 female connector, angled, 8-pin, cable length: 2 m, jacket material: PUR, black; cULus approval