


REM-105SA0C-9D32B-B1M12/N46

Absolute Rotary Encoder - Multiturn Industrial Line





Technical data

Type	REM-105SA0C-9D32B-B1M12/N46
ID	100011421
Measuring principle	Optical
General data	
Max. rotational speed	8000 rpm
Moment of inertia of the rotor	$3 \times 10^{-6} \text{ kgm}^2$
Absolute accuracy	$\pm 0.015^\circ$ At 25 °C
Output type	Absolute multiturn
Electrical data	
Operating voltage U_B	10...30 VDC
No-load current	$\leq 80 \text{ mA}$
Short-circuit protection	yes
Wire break/reverse polarity protection	yes
Communication protocol	CANopen
Interface	CAN High-Speed in accordance with ISO 11898, basic and full CAN, CAN specification 2.0 B
Node ID	1...127 mit Software konfigurierbar; Werkseinstellung: 63
Baud rate	10 kbps to 1000 kbps software configurable
Mechanical data	
Flange type	Clamping flange
Flange diameter	$\varnothing 58 \text{ mm}$
Shaft Type	Solid shaft
Shaft diameter D (mm)	6.35
Shaft diameter D	0.25 in

Features

- Clamping flange, $\varnothing 58 \text{ mm}$
- Solid shaft, $\varnothing 6.35 \text{ mm} \times 22.225 \text{ mm}$
- Optical measuring principle
- Shaft material: stainless steel
- Protection class IP67 on housing and shaft side
- $-40 \dots +80^\circ \text{C}$
- Max. 8000 rpm (continuous operation 5000 rpm)
- 10...30 VDC
- CANopen
- M12 $\times$ 1 male, 5-pin
- Singleturn resolution 14 bit scalable, default 14 bit
- Multiturn resolution scalable up to 16 bit over total resolution
- Total resolution 32 bit scalable, default: 32 bit

Wiring diagram



Technical data

Shaft Length L [mm]	22.225
Shaft length X	0.875 in
Shaft material	Stainless steel
Housing material	Die-cast zinc
Electrical connection	Connector, M12 × 1
	5-pin
Axial shaft load	40 N
Radial shaft load	80 N
Environmental conditions	
Ambient temperature	-40...+80 °C
Vibration resistance (EN 60068-2-6)	10 g (100 m/s²), 55...2000 Hz
Shock resistance (EN 60068-2-27)	250 g (2500 m/s²), 6 ms
Protection class	IP67
Protection class shaft	IP67

Accessories

Dimension drawing	Type	ID	
	FSM-2FKM57	6622101	CANopen/DeviceNet/power supply T-splitter, 1 × M12 male connector, 2 × M12 female connector, 5-pin
	RKC5701-5M	6931034	Bus cable for CAN (DeviceNet, - CANopen), M12 female connector, straight, cable length: 5 m, jacket material: PUR, anthracite; cULus approval