


Accessories Compression Fitting For Temperature Sensors CF-M-6.35-N1/2-A4



- Compression fittings for direct mounting of TP temperature probes
- Metal compression fitting
- For probe with 6.35-mm diameter
- N1/2" process connection, male thread

General description

With compression fittings, probes can be mounted directly where they are needed and they can be immersed as deep as wanted. Through direct contact with the medium, they react immediately to temperature changes.

Туре	CF-M-6.35-N1/2-A4	
ID	100027548	
Temperature range		
Mechanical data		
Housing material	Stainless steel, 1.4404 (AISI 316L)	
Sealing material	stainless steel	
Process connection	1/2" NPT male thread	
Pressure resistance	100 bar	
Max. tightening torque of housing nut	100 Nm	



Accessories

Type code	Ident no.		Dimension drawing
CF-M-6.35-G1/2-A4	100027547	Compression fitting for direct mounting of temperature probes; probe diameter 6.35 mm; G1/2" process connection, male thread	- 143,328
CF-M-6.35-N1/2-A4	100027548	Compression fitting for direct mounting of temperature probes; probe diameter 6.35 mm; N1/2" process connection, male thread	10 MP 1 13 30 MB 2 10 MP 1 10