


AD-FK5PL-FS5PL
Wall Feedthrough



Technical data

Type	AD-FK5PL-FS5PL
ID	100048192
Connector A	Female, M12 × 1, Straight, L-coded
Number of pins	4+FE
Contacts	Brass, CuZn, Gold-plated
Contact carriers	Plastic, PA, Black
Connector body	Die-cast Zinc, GD-Zn, Silver
Coupling nut/screw	Brass, CuZn, Nickel-plated
Tightening torque (range)	0.6 ... 0.8 Nm (observe max. torque of mating connector!)
Mechanical lifespan	> 100 Mating cycles
Protection class	IP67, (screwed together)
Connector B	Male, M12 × 1, Straight, L-coded
Number of Pins	4+FE
Contacts	Brass, CuZn, Gold-plated
Contact carriers	Plastic, TPU, Black
Connector body	Die-cast Zinc, GD-Zn, Silver
Coupling nut/retaining screw	Brass, CuZn, Nickel-plated
Tightening torque	0.6 ... 0.8 Nm (observe max. torque of mating connector!)
Mechanical life	> 100 Mating cycles
Protection class	IP67, (Screwed together)
Electrical properties at +20 °C	
Rated voltage	63 V
Current	16 A
Mechanical and chemical properties	
Ambient temperature (fixed)	-30...+80 °C


Features

- M12 female connector — M12 male connector
- L-coded, 4+FE
- RoHS compliant
- Protection class: IP67

Contact assignment



Circuit Diagram



Technical data

Approvals

cULus recognized
